



## Measuring leads

### MLN 200/2,5



Product	MLN 200/2,5
description	Measuring lead, at either end 4 mm diameter plug with caged spring and 4 mm diameter socket for tower construction. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.
operating instruction	BA401
article-no. / *colour	9340661xx  00 black   01 red   02 blue   03 yellow   04 green   05 brown   06 gray   07 white   09 violet   88 yellow green <div style="text-align: right;"><b>Ni</b></div>
drawing	
technical data	
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	0 <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	32 A
material plug	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 <sup>(2)</sup>	-15 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2
cable length	200 cm

4 mm system

conductor size	2,5 mm <sup>2</sup>
cable material	PVC
contact resistance	20 mOhm
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> Other circuits that are not directly connected to mains

stand: 20.07.2018