

BLINDNIETE


FLACHRUNDKOPF (~ DIN EN ISO 16582)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 16582)


RIVETS AVEUGLES

TÊTE PLATE (~ DIN EN ISO 16582)










Kupfer Legierung
Copper alloy
Cuivre alliage

Stahl verzinkt
Steel zinc plated
Acier zingué










Ø 3,0 mm

D1 = 3,0 + 0,08 / - 0,1 mm
D2 = 6,5 + 0 / - 0,7 mm
k = 0,8 + / - 0,2 mm
d = 1,75 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,1 mm


	F-Max		CODE				
3,0 x 4,0 mm	8,4 mm	0,5 - 1,5 mm	70501 30400	600 N	700 N	1000	10000
3,0 x 6,0 mm	10,4 mm	1,0 - 3,0 mm	70501 30600			1000	10000
3,0 x 8,0 mm	12,4 mm	3,0 - 5,0 mm	70501 30800			1000	10000
3,0 x 10,0 mm	14,4 mm	5,0 - 7,0 mm	70501 30100			1000	10000
3,0 x 12,0 mm	16,4 mm	7,0 - 9,0 mm	70501 30120			1000	10000







Ø 3,2 mm

D1 = 3,2 + 0,08 / - 0,1 mm
D2 = 6,5 + 0 / - 0,7 mm
k = 0,8 + / - 0,2 mm
d = 1,95 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm


	F-Max		CODE				
3,2 x 6,0 mm	10,9 mm	1,0 - 3,0 mm	70501 32600	700 N	800 N	1000	10000
3,2 x 8,0 mm	12,9 mm	3,0 - 5,0 mm	70501 32800			1000	10000
3,2 x 10,0 mm	14,9 mm	5,0 - 7,0 mm	70501 32100			1000	10000
3,2 x 12,0 mm	16,9 mm	7,0 - 9,0 mm	70501 32120			1000	10000







Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,15 mm
D2 = 8,0 + 0 / - 1,0 mm
k = 1,0 + / - 0,3 mm
d = 2,1 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

	F-Max		CODE				
4,0 x 6,0 mm	10,9 mm	1,0 - 2,0 mm	70501 40600	1000 N	1500 N	1000	10000
4,0 x 8,0 mm	12,9 mm	2,0 - 4,0 mm	70501 40800			1000	10000
4,0 x 10,0 mm	14,9 mm	4,0 - 6,0 mm	70501 40100			1000	10000
4,0 x 12,0 mm	16,9 mm	6,0 - 8,0 mm	70501 40120			1000	10000
4,0 x 14,0 mm	18,9 mm	8,0 - 10,0 mm	70501 40140			500	5000
4,0 x 16,0 mm	20,9 mm	10,0 - 12,0 mm	70501 40160			500	5000

Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm
D2 = 9,5 + 0 / - 1,0 mm
k = 1,1 + / - 0,3 mm
d = 2,7 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,9 mm

	F-Max		CODE				
4,8 x 8,0 mm	13,4 mm	1,5 - 3,5 mm	70501 48800	1500 N	2000 N	500	5000
4,8 x 10,0 mm	15,4 mm	3,5 - 5,5 mm	70501 48100			500	5000
4,8 x 12,0 mm	17,4 mm	5,5 - 7,5 mm	70501 48120			500	5000
4,8 x 14,0 mm	19,4 mm	7,5 - 9,5 mm	70501 48140			500	5000
4,8 x 16,0 mm	21,4 mm	9,5 - 11,5 mm	70501 48160			500	5000
4,8 x 18,0 mm	23,4 mm	11,5 - 13,5 mm	70501 48180			500	5000
4,8 x 20,0 mm	25,4 mm	13,5 - 15,5 mm	70501 48200			500	5000