

## Spiro drill chuck

Precision design



### Application:

For clamping and releasing drill bits quickly without a key.

### Execution:

- Permanent and automatic retightening.
- Hardened wear parts.
- Particularly suitable for high rotation speeds on drills and boring mills.
- With internal taper chuck in accordance with DIN 238.

### Advantage:

- High concentricity < 0.05 mm.



<b>Art. no.</b>	<b>21305 090</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	87 1017
<b>Min./max. clamping width</b>	3-16 mm
<b>Suitable for taper</b>	B 18
<b>Outer diameter</b>	55 mm
<b>Length closed</b>	106.8 mm
<b>Gross Weight</b>	1.533 kg
<b>Product Group</b>	201

### EAN

4019208009445