

## Screw tap, HSSE M ISO 2X (6HX) 45° (right) 371 C

for universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For producing metric threads on CNC machines or conventional machines in **blind holes** in steel, stainless steel, non-ferrous metals, cast iron and special alloys up to 1200 N/mm<sup>2</sup>.

### Advantage

- Ideal for long service life requirements and materials that are difficult to machine, such as stainless steel
- Innovative cutting geometry ensures high process reliability even under difficult machining conditions

<b>Art. No.</b>	<b>13078 200</b>
<b>Type</b>	UNI MAX 45 Control
<b>Thread type</b>	Metric thread
<b>Thread type x nominal diameter</b>	M20
<b>Pitch</b>	2.5 mm
<b>Hole type</b>	Blind hole ≤ 2.5xD
<b>Cutting material</b>	HSSE
<b>Surface</b>	Vaporised
<b>Lead angle shape</b>	C
<b>Tolerance of screw taps</b>	ISO 2X (6HX)
<b>Twist angle</b>	45° (right)
<b>Shaft diameter</b>	16 mm
<b>Application type/machine type</b>	CNC, Conventional
<b>Core hole diameter</b>	17.5 mm
<b>Coolant supply</b>	External
<b>Length</b>	140 mm
<b>Shank square</b>	12 mm
<b>Overall stainless steel suitability</b>	0
<b>fitness not iron total</b>	0
<b>fitness Titan/Nickel/Super total</b>	0
<b>DIN</b>	376

### EAN-Code

4050293651324