

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



# Technical Datasheet

## tasker® C708 U.T.P. CCA Cat. 5e

### 4x2x0,14 mm<sup>2</sup> - UL/ETL verified Cable



A	B	C	D
---	---	---	---

**ETHERSOUND**  
**CATEGORY**

Stranded conductors EIA/TIA 568-suitable not only for RJ 45 8 Pin.  
 Data Transmission Cable (See Audio Catalogue).

- A:** Grey Soft **PVC** Sheath. Outer Cable Diam. Ø 5,00 (±0,10) mm.
- B:** The four pairs are stranded together with polyester based tape.
- C:** Insulation with PE – Diam. Ø 0,90 (±0,10) mm.  
 RJ45 plug connector compatible.  
 Core colors: White – Blue/Blue White-Orange/ Orange, White-Green/Green,  
 White-Brown/Brown.
- D:** Stranded formation of 7x0,16 mm in CCA.  
 Nom. Cross section 4x2x0,14 mm<sup>2</sup>.

**MARKING**  
**CUSTOM**

**tasker®** C708 U.T.P. cat. 5e 4Px24AWG CCA Stranded ISO 1801 100 MHz  
 This product is also available in **L.S.Z.H.** polymer, **PE**, **PUR**, with or  
 without **Steel Armor**.

**Cable Properties**

<b>Conductor Resistance</b>	170 Ω/Km ± 5%
<b>Impedance</b>	100 Ω± 5%
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<input checked="" type="checkbox"/>	Fixed	Fissa	<b>INFORMATION</b>	<input checked="" type="checkbox"/>	RoHS2 Compliant
<b>Impiego</b>	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	<b>Posa</b>	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	<input checked="" type="checkbox"/>	Ver. B / 18.07.2016
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			