

SSSC clamp holder, positive, right-hand

for facing and longitudinal turning using SC indexable inserts

ATORN[®]

Application

for face and longitudinal turning with SC indexable insert 90°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- sturdy geometry for use in challenging conditions
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing



| | |
|---------------------------------------|---------------------------|
| Art. no. | 17834 208 |
| ISO name | SSSC R/L 2525 M12 IK G1/8 |
| Shaft height | 25 mm |
| Shank width | 25 mm |
| Length | 150 mm |
| Length of head | 25 mm |
| Programming size | 32 mm |
| Suitable for indexable inserts | SC.. 1204.. |
| Tool design | Right |

EAN-Code

4050293449846