

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

FRC


ORS Female Swivel, 90° Elbow, long drop
 ORS-Anschluss, 90° Krümmer, langer Schenkel
 Femelle ORS coudé 90°, long
 Femmina ORS a 90° gomito flangiato lungo
 Hembra loca ORS acodado a 90°, coda largo°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G4FRC4	1S4FRC4	1A4FRC4	9/16-18				-4	53,0	29,6	45,7	4,2	17		
1G6FRC6	1S6FRC6	1A6FRC6	11/16-16				-6	59,4	34,1	54,1	6,2	22		
1G8FRC8	1S8FRC8	1A8FRC8	13/16-16				-8	72,1	42,4	63,8	9,4	24		
1G10FRC10	1S10FRC10		1-14				-10	78,0	48,6	70,1	11,7	30		
1G12FRC12	1S12FRC12	1A12FRC12	1 3/16-12				-12	88,7	58,5	96,0	14,8	36		
1G16FRC16	1S16FRC16	1A16FRC16	1 7/16-12				-16	107,3	72,9	114,3	19,3	41		
1G20FRC20	1S20FRC20	1AP20FRC20*	1 11/18-12				-20	134,6	90,6	129,3	25,7	50		
		1AT20FRC20**	1 11/16-12				-20	134,6	90,7	129,3	25,7	50		

MR

Male ORS
 ORS-Außengewinde
 Mâle ORS
 Maschio ORS
 Macho ORS



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G6MR4	1S6MR4	1A6MR4	11/16-16UN				-4	47,7	24,4		4,2	19		
1G6MR5	1S6MR5	1A6MR5	11/16-16UN				-5	48,3	23,9		5,3	19		
1G6MR6	1S6MR6	1A6MR6	11/16-16UN				-6	50,5	25,2		6,7	19		
1G8MR6	1S8MR6	1A8MR6	13/16-16UN				-6	49,6	24,3		6,7	22		
1G10MR8	1S10MR8	1A10MR8	1-14UN				-8	61,1	31,4		9,6	27		
1G12MR10	1S12MR10	1A12MR10	1 3/16-12UN				-10	65,9	36,5		12,8	32		
1G12MR12	1S12MR12	1A12MR12	1 3/16-12UN				-12	66,8	36,6		15,5	32		
1G16MR12	1S16MR12	1A16MR12	1 7/16-12UN				-12	65,0	34,8		15,5	41		
1G16MR16	1S16MR16	1A16MR16	1 7/16-12UN				-16	76,2	41,8		20,6	41		
1G20MR16	1S20MR16	1A20MR16	1 11/16-12UN				-16	76,2	41,8		20,6	46		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice