

Ring bolt incl. Key

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

Delivery:

Includes Key



Art. no.	77232 212
Brand	CARTEC
Manufacturer Part Number	C807XCHT12
Design	With key
Thread dimension	M12
Load-carrying capacity	0.75 t
Distance between lower edge of retainer holder and retainer	41.5 mm
Bracket width	11.5 mm
Bracket height	12.5 mm
Outer diameter	55.5 mm
Diameter 2	36.5 mm
Internal width	30 mm
Width of support plate	30.6 mm
Usable thread length	18 mm
Width across flats	8 mm
Weight	0.2 kg
Gross Weight	0.200 kg
Product Group	775

EAN

8013429916748