

HEATER BLOWER WITH CLIP AND THERMOSTAT  
CS 130 230 V AC, 1200 W, 0 - 60 DEG C



Figure similar

Model		
product brand name		SIVACON
General technical data		
Active power consumption / Rated value	W	400
Volume flow rate / free-blowing	m <sup>3</sup> /h	160
Voltage		
Continuous heat output / at 20 °C	W	1 200
Inrush current / typical	A	16
Protection class		
Protection class IP		IP20
Main circuit		
Operating voltage		
• Rated value / minimum	V	230
• Rated value / maximum	V	230
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230
Operating current / of the slow-blow fuse link	A	8
Adjustable parameters		
Adjustable temperature		
• initial value	°C	0
• Full-scale value	°C	60
Product details		

<b>Product component</b>		
• blower		Yes
• Thermostat		Yes

### Connections

Tightening torque / with screw-type terminals / maximum	N·m	0.8
---	-----	-----

### Mechanical Design

Height	mm	182
Width	mm	160
Depth	mm	120
Material / of the enclosure		plastic

### Environmental conditions

Relative humidity / Reference value	%	90
-------------------------------------	---	----

### Certificates

<b>Equipment marking</b>		
• acc. to DIN EN 61346-2		R
• acc. to DIN EN 81346-2		E

### General Product Approval



### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21503A>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8MR21503A/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR21503A](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR21503A)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015