



Figure similar

FILTER FAN AIR FLOW FREE AIR 531 M3 PER H
 CUT OUT 292X292 MM 230 V AC RAL 7035 INPUT
 POWER 64W DEGREE OF PROTECTION IP 55

Model		
product brand name		SIVACON
Product designation		filter fan
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
A-rated sound power level / maximum	dB	60
Active power consumption / Rated value	W	64
Cutout width	mm	292
Cutout height	mm	292
Operating period	h	40 000
Operating temperature / minimum	°C	-10
Cooling capacity / at 35 °C	W	114.1
Rotor speed / at 50 Hz / Rated value	1/min	2 550
Rotor speed / at 60 Hz / Rated value	1/min	2 800
Protection class		
Protection class IP		IP55
Electricity		
Consumed current / minimum	A	0.29
Main circuit		
Operating voltage		
<ul style="list-style-type: none"> with AC / at 50 Hz / Rated value / maximum 	V	230
<ul style="list-style-type: none"> with AC / at 60 Hz / Rated value / maximum 	V	230

Appearance

Color		RAL 7035
-------	--	----------

Product details

Product component / Fan		No
-------------------------	--	----

Number

Number of ventilators		1
-----------------------	--	---

Mechanical Design

Height	mm	323
--------	----	-----

Width	mm	323
-------	----	-----

Depth	mm	154
-------	----	-----

Mounting type		snap-on mounting
---------------	--	------------------

Mounting type		No
• 19-inch installation		Yes
• wall mounting		

Material		plastic
----------	--	---------

Certificates

Equipment marking		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR65235LV60>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR65235LV60/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR65235LV60

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015