

Connection Cable

M12 × 1; 12-pin

ZDCV002



Part Number



Technical Data

Mechanical Data	
Connection 1	Socket, straight
Connection mode 1	M12 × 1, 12-pin
Connection 2	Plug, straight
Connection mode 2	M12 × 1, 12-pin
Torque	M12: 0,6 Nm
Cable Length	5 m
Cable Diameter	6,5 mm
Wire cross-section	0,14 mm ²
Degree of Protection	IP67
Temperature Range	-25...85 °C
Cable Jacket Material	PUR
Material Wire Insulation	TPE
Material Sleeve Nut	CuZn, nickel-plated
Screened	yes
Halogen-free	yes
Drag Chain Suitable	yes
Bending radius (fixed installation)	5 × d
Bending radius (used in motion)	10 × d
Travel speed (with 5 m horizontal travel distance)	≤ 3,3 m/s
Acceleration	≤ 5 m/s ²
Bending cycles	≤ 5000000
Packaging unit	1 Piece
Connection Diagram No.	S90
Connection Equipment No.	87

- Drag chain suitable
- PUR, straight
- Screened



Legend					
+	Supply Voltage +	PT	Platinum measuring resistor	EN _A S ₉₀	Encoder A/A (TTL)
-	Supply Voltage 0 V	nc	not connected	EN _B S ₉₀	Encoder B/B (TTL)
~	Supply Voltage (AC Voltage)	U	Test Input	EN _A	Encoder A
A	Switching Output (NO)	Ū	Test Input inverted	EN _B	Encoder B
Ā	Switching Output (NC)	W	Trigger Input	AMIN	Digital output MIN
V	Contamination/Error Output (NO)	W-	Ground for the Trigger Input	AMAX	Digital output MAX
Ṽ	Contamination/Error Output (NC)	O	Analog Output	AOK	Digital output OK
E	Input (analog or digital)	O-	Ground for the Analog Output	SY in	Synchronization In
T	Teach Input	BZ	Block Discharge	SY OUT	Synchronization OUT
Z	Time Delay (activation)	AW	Valve Output	DiT	Brightness output
S	Shielding	a	Valve Control Output +	M	Maintenance
RxD	Interface Receive Path	b	Valve Control Output 0 V	rsv	reserved
TxD	Interface Send Path	SY	Synchronization	Wire Colors according to DIN IEC 757	
RDY	Ready	SY-	Ground for the Synchronization	BK	Black
GND	Ground	E+	Receiver-Line	RD	Brown
CL	Clock	S+	Emitter-Line	OG	Orange
E/A	Output/Input programmable	≡	Grounding	YE	Yellow
⊕	IO-Link	SnR	Switching Distance Reduction	GN	Green
PoE	Power over Ethernet	Rx+/-	Ethernet Receive Path	BU	Blue
IN	Safety Input	Tx+/-	Ethernet Send Path	VT	Violet
QSSD	Safety Output	Bus	Interfaces-Bus A(+)/B(-)	GY	Grey
Signal	Signal Output	La	Emitted Light disengageable	WH	White
BL-D+/-	Ethernet Gigabit bidirect. data line (A-D)	Mag	Magnet activation	PK	Pink
EN ₀ S ₉₀	Encoder 0-pulse 0-0 (TTL)	RES	Input confirmation	GNYE	Green/Yellow
		EDM	Contactor Monitoring		

Specifications are subject to change without notice