

# NE8FBV-C5-LED1

Vertical PCB mount RJ45 receptacle, CAT5e, two light pipes for SMD-LEDs, B-Series cutout with latch lock, max. panel thickness 3 mm

The etherCON Series is a ruggedized and lockable RJ45 connector system, optimized for pro audio, video and lightning network applications. The chassis connectors are shaped to fit into standardized panels out of the entertainment industry.

The B-Series offers a space saving design and a rugged metal front plate.

Attention! Does not intermate with CAT6 cable connectors.

**Available from May 2015**

## Features & Benefits

- Vertical PCB design at 24 mm distance to front panel – fits the widely accepted industry standard dimension for XLRs, 1/4" jacks etc.
- Accommodates rugged etherCON NE8MC\* or any standard RJ45 plug
- Approved latch lock system
- Ground panel connection
- PoE+ compliant according to 802.3at Type2
- CAT5e performance according to ISO/IEC 11801 and TIA/EIA 568-C.2

## Technical Information [hide](#)

Product	
Title	NE8FBV-C5-LED1
Gender	female
Electrical	
Contact resistance	< 10 mΩ (inner)
Dielectric strength	1 kVdc
Frequencyrange	1 - 100 MHz
Insulation resistance	> 0.5 GΩ
Rated current per contact	1.5 A
Rated voltage	< 50 V
Transmission performance	CAT5e, acc. TIA/EIA 568C.2, IEC11801
Power over Ethernet	PoE+ acc. IEEE 802.3at
Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Panel thickness	max. 3 mm (0.12")
Wiring	vertical PCB mount
Locking device	Latch lock
Mounting direction	rear
Chassis shape	B



## Image gallery



**Material**

Contact plating	0.2 µm Au over Ni plating
-----------------	---------------------------

Contacts	Bronze (CuSn8)
----------	----------------

Shell	PBT D202G30
-------	-------------

**Environmental**

Flammability	UL 94 V-0
--------------	-----------

Solderability	Complies with IEC 68-2-20
---------------	---------------------------

Temperature range	-30 °C to +80 °C
-------------------	------------------