LED Ultra Blue / Green, 3mm



RoHS Compliant



Specifications:

Dice material : InGaN
Emitted colour : Blue Green
Lens colour : Water Clear
Peak wavelength : 505nm
Viewing angle : 36°
Luminous intensity (IV) : 3,650mcd

Absolute Maximum Ratings (T_a = 25°C)

Reverse Voltage	5V		
Reverse Current	10μA (V _R = 5V)		
Electrostatics Discharge (ESD)	200V		
Operating Temperature Range	-40°C to 85°C		
Storage Temperature Range	-40°C to 100°C		
Lead Soldering Temperature Range 1.6mm (1/16 inch) from body	260°C for 5 Seconds		


Electrical/Optical Characteristics at T_a = 25°C


Parameter	Symbol	Minimum	Typical	Maximum	Unit	Test
Luminous Intensity	IV	1,800	3,650	5,200	mcd	IF = 20mA
Viewing Angle	2θ 1/2	-	36	-	degrees	IF - ZUITA
Peak Emission Wavelength	λP	-	505	-		-
Dominant Wavelength	λD	-	510	-	nm	-
Spectral Line Half-Width	Δλ	-	40	-		-
Forward Voltage	VF	2.7	3.4	4	V	IF = 20mA
Power Dissipation	Pd	-	-	85	-	-
Peak Forward Current (Duty 1/10 at 1KHz)	IF (Peak)	-	-	100	-	-
Recommended Operating Current	IF (Rec)	-	20	-	mA	-

LED Ultra Blue / Green, 3mm





Blue Green (InGaN $\lambda P = 505$ nm)





Blue Green (InGaN $\lambda P = 505$ nm)






Luminous Intensity vs. Ambient Temperature


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



LED Ultra Blue / Green, 3mm







Dimensions: Millimetres (Inches)

Part Number Table

Description	Part Number		
LED, 3mm, 32°, Ultra-Blue/Green	MCL034BGC		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

