
Surface-Mount Low V_F Standard Rectifiers



SE20DX Anode 1 O K



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS					
I _{F(AV)}	20 A				
V _{RRM}	400 V, 600 V				
I _{FSM}	200 A				
V_F at I_F = 20 A (T_A = 125 °C)	0.85 V				
T _J max.	175 °C				
Package	SMPD (TO-263AC)				
Circuit configuration	Single				

FEATURES

- Very low profile typical height of 1.7 mm
- Low forward voltage drop
- AEC-Q101 qualified available
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose, power line polarity protection, in both consumer and automotive applications.

MECHANICAL DATA

Case: SMPD (TO-263AC) Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 and HM3 suffix meet JESD 201 class 2 whisker test

Polarity: as marked

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)						
PARAMETER		SE20DLG	SE20DLJ	UNIT		
Device marking code		SE20DLG	SE20DLJ			
Maximum repetitive peak reverse voltage		400	600	V		
Marine DO face and a second	I _F ⁽¹⁾	20		A		
Maximum DC forward current	I _F ⁽²⁾	3.9				
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I _{FSM}	200		А		
Operating junction and storage temperature range	T _J , T _{STG} ⁽³⁾	-55 to +175		°C		

Notes

⁽¹⁾ Mounted on infinite heatsink

⁽²⁾ Free air, mounted on recommended copper pad area

 $^{(3)}$ The heat generated must be less than the thermal conductivity from junction to ambient dP_D/dT_J < R_{thJA}

Document Number: 87488



RoHS

COMPLIANT

HALOGEN

FREE





ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I _F = 10 A	T _A = 25 °C		0.86	-	V
	I _F = 20 A		V _E ⁽¹⁾	0.95	1	
	I _F = 10 A	– T _A = 125 °C	VF	0.73	-	
	I _F = 20 A			0.85	0.9	
Reverse current	Datad V	T _A = 25 °C	– I _R ⁽²⁾	-	5	μA
	Rated V _R	T _A = 125 °C	IR (=/	13	100	
Typical reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	330	-	ns
Typical junction capacitance	4.0 V, 1 MHz		CJ	160	-	pF

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

⁽²⁾ Pulse test: Pulse width \leq 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °c unless otherwise noted)						
PARAMETER	SYMBOL	SE20DLG	SE20DLJ	UNIT		
Typical thermal resistance	R _{0JA} (1)(2)	55		°C/W		
Typical thermal resistance	R _{0JM} ⁽³⁾	1				

Notes

 $^{(1)}$ The heat generated must be less than the thermal conductivity from junction-to-ambient: $dP_D/dT_J < 1/R_{\theta JA}$

⁽²⁾ Free air, mounted on recommended PCB, 2 oz. pad area; thermal resistance R_{0.JA} - junction to ambient to follow JEDEC[®] 51-2A

(3) Mounted on infinite heatsink thermal resistance R_{thJM} - junction to mount to follow JEDEC[®] 51-14 transient dual interface test method (TDIM)

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SE20DLJ-M3/I	0.543	I	2000/reel	13" diameter plastic tape and reel		
SE20DLJHM3/I ⁽¹⁾	0.543	I	2000/reel	13" diameter plastic tape and reel		

Note

⁽¹⁾ AEC-Q101 qualified



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25 \text{ °C}$ unless otherwise noted)




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics






Fig. 5 - Typical Junction Capacitance





Revision: 16-Apr-2020


3

Document Number: 87488

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.