

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0436501015**

Status: **Active**

Overview:

Description: Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Single Row, 10 Circuits, with PCB Polarizing Peg, Tin, Glow-Wire Capable, Black

Documents:

- | | |
|---|--|
| Drawing (PDF) | Test Summary 430450004-TS-000 (PDF) |
| 3D Model | Test Summary TS-43045-001-001 (PDF) |
| 3D Model (PDF) | Test Summary TS-43045-002-001 (PDF) |
| Product Specification 436500001-PS-JA-000 (PDF) | Test Summary TS-46235-001-001 (PDF) |
| Product Specification 436500001-PS-KO-000 (PDF) | Datasheet (PDF) |
| Product Specification 436500001-PS-SP-000 (PDF) | Symbol Footprint Data SYM-43650-1015-001 (PDF) |
| Product Specification PS-43650-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-70873-0811-001 (PDF) | |

Agency Certification

CSA	LR19980
UL	E29179


General

Product Family	PCB Headers
Series	43650
Application	Power, Wire-to-Board
Comments	<p>High Temperature Square Pin<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.</p>

Overview	microfit_30
Product Name	Micro-Fit 3.0
UPC	800754016377

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Capable	Yes
Mated Height	17.27mm
Material - Metal	Brass



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43650 Series

Mates With

Micro-Fit 3.0 Receptacle Housing [43645](#)

Micro-Fit 3.0 TPA Receptacle Housing
[171850](#)
 Micro-Fit 3.0 Cable Assembly
[2147501101](#) , [2147501102](#) , [2147501103](#) ,
[2147511101](#) , [2147511102](#) , [2147511103](#)

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.589/g
Number of Rows	1
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Kinked Pin

Electrical

Current - Maximum per Contact	8.5A
Voltage - Maximum	600V

Solder Process Data

Duration at Max. Process Temperature (seconds)	030
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-0811-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	SD-43650-006-001
Symbol/Footprint Data	SYM-43650-1015-001
Test Summary	430450004-TS-000, TS-43045-001-001, TS-43045-002-001, TS-46235-001-001

This document was generated on 03/21/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION