

Socketed charger Datasheet

Ideal for fleet service operators and workplace charging. EVS7GGR-02 model.

Commercial grant approved, for more information see: www.gov.uk/transport/low-emission-and-electric-vehicles



- Features Wi-Fi/LAN+4G+RFID
- Fully compliant with The Electric Vehicles (Smart Charge Points) Regulations 2021, including Schedule 1
- Full Smart! functionality •
- Dynamic charging up to 7.4 kW (32A) •
- No earth rod required integrated open PEN • conductor protection
- Safe integrated Type A RCD
- OCPP 1.6J connectivity free lifetime • over-the-air updates
- Type 2 socket with auto-lock
- Commercial grant approved

- Manageable, smart and secure business charging solution
- X Quick and easy installation, with UK based technical support

DEKF

- 3 year warranty, DEKRA certified & regulations compliant
- - Compatible with all electric and hybrid plug-in vehicles



View the full range at **syncev**.co.uk

SOCKETED RANGE FEATURES

CODE :	EVS7GGR-02 (WI-FI / LAN / 4G / RFID)	WI-FI & ETHERNET :	2.4Ghz 802.11 B/G/N/E/I & RJ45
TYPE :	SOCKETED	WI-FI SECURITY :	WPA/WPA2/WPA2-ENTERPRISE/WPS
SOCKET/PLUG :	TYPE 2 SOCKET WITH AUTO LOCK	BLUETOOTH :	4.2 BR/EDR and BLE
кพ :	7.4KW 32A MODE 3	RFID :	SUPPORTS ISO14443, READS M1 CARDS
MIN CHARGE CURRENT :	CONFIGURABLE, 6 - 32A	CONNECTION PROTOCOL :	OCPP 1.6J
ELECTRICAL INPUT :	220-240V, 50-60Hz, SINGLE PHASE	4G DATA :	3 YEARS INCLUDED, WHEN USED WITH SYNC EV. TOP-UP ONLINE TO
COLOUR :	BASE & TRIM - RAL 9005 (BLACK) BODY - RAL 7016 (GRAPHITE GREY)	APP AND BACK OFFICE :	CONTINUE SERVICE AFTER 3 YEARS SYNC EV (SUPPORTS IN-APP PAYMENT*)
CABLE MANAGEMENT :	BUILT IN CABLE WRAP	OPERATING TEMP :	-25 TO +40°C
PEN PROTECTION :	YES, IN-BUILT EARTH DISCONNECTION	SOFTWARE & FIRMWARE	OVER-THE-AIR
EARTH ROD :	NOT REQUIRED	UPGRADE : WARRANTY :	3 YEARS
RCD PROTECTION :	YES, 6mA DC, 30mA TYPE-A, IN-BUILT	STANDARDS &	IEC61851-1, IEC61439-7, IEC 62955, IC
OVERLOAD AND FAULT PROTECTION :	OVER CURRENT AND FAULT PROTECTION	APPROVALS :	61851-21-2, BS EN62196, EN301 511, EN 301 908-1/2/13, EN 301 489-3,
ELECTRICAL CLASS :	CLASS 1, HOUSING CLASS 2		EN 300 330, EMC COMPLIANT, CE, UKCA, DEKRA CERTIFIED, THE ELECTRIC
LOAD BALANCING :	VIA OPTIONAL ACCESSORY (ORDER SEPARATELY, CODE : EVA120CT1)		VEHICLES (SMART CHARGE POINTS) REGULATIONS 2021 INCLUDING SCHEDULE 1
CONSUMER UNIT	40A MCB OR 30mA TYPE-A RCD		
REQUIREMENTS :	(DEPENDENT ON CABLE TYPE &/OR ROUTE)	SUPPLIED ACCESSORIES :	5X BASE FIXING CAPS, 5X ASSEMBLY LID BOLTS, 1X BLANKING PLUG AND 1X
TERMINALS :	FIRST FIX PLUG CONNECTOR		25MM COMPRESSION GLAND, USER- SIDE CONNECTOR, CORD GRIP AND
INDICATOR :	RGB LED AND BUZZER		2X CORD GRIP ASSEMBLY SCREWS
INDICATOR MODES :	BLUE - STANDBY, FLASHING BLUE - PREPARING, GREEN - CHARGING,	DIMENSIONS (MM) :	297 (H) X 224 (W) X 123 (D)
	YELLOW - NO NETWORK, RED - ERROR	ADDITIONAL :	
HOUSING :	UV STABILISED POLYCARBONATE		PROTECTION, BLUETOOTH TO BLUETOOTH COMMISSIONING, BUILT-IN
WALL FIXING :	4 POINT WITH HORIZONTAL AND		SPIRIT LEVEL
	VERTICAL ADJUSTMENT, SUPPLIED FIXING HOLE TEMPLATE. FIXING HOLE	ACCESSORIES :	SINGLE CHARGER STAND (EVASTAND12S)
	CENTRES : 110 HORIZONTAL, 145 VERTICAL (MM)		TWIN CHARGER STAND (EVASTAND12T)
IP / IK RATING :	IP55 / IK10		LOAD MANAGEMENT KIT (EVA120CT1)
SOC MODULE :	AI ESP32-S SOC		CHARGING CABLES (VARIOUS OPTIONS, SEE SYNCEV.CO.UK)





*Email our team at workplace@syncev.co.uk for more information

