Plastic Fiber-Optic Cable

Reflex Mode

K15

Part Number



- Especially suitable in applications where only minimal space is available
- Fiber-optic cable can be cut to length by the cutting tool

Technical Data

Optical Data		
Fiber Core Diameter	0,5 mm	
Fiber Core	PMMA	
Fiber	Step Index	
Fiber Distribution	coaxial arrangement	
Range with Sensor Type	60 mm	
Range with LA27	1030 mm	
Opening Angle	55 °	
Light Spot Diameter with LA27	see Table 1	
Mechanical Data		
Temperature Range	-4085 °C	
Bending Radius	15 mm	
Fiber-Optic Length	2 m	
Jacket Material	PE (black)	
Material End Sleeve	Stainless Steel	
Jacket Diameter	1,3 mm	
Light Emission	straight	
Suitable Mounting Technology No.	310	

Table 1

Detection Range	10 mm	20 mm	30 mm
Light Spot Diameter	0,5 mm	1 mm	2 mm

Complementary Products

Lens LA27

The plastic fiber-optic cables are very flexible and can be especially used in applications where minimal space is available. Plastic fiber-optic cables are provided in standard length of 2 meters. Special lengths up to 50 meters are available as well. Plastic fiber-optic cables can be cut to length by the user with the help of the cutting tool Z0015.





