



IQXO-64x

IQXO-64x

Standard 1.6 x 1.2mm crystal oscillator in a ceramic package with a seam sealed metal lid, hermetically sealed

Model Name	Description
IQXO-640	A 3.3V version
IQXO-641	A 2.5V version
IQXO-642	A 1.8V version

ISSUE 4; October 2021

Description

- Standard 1.6 x 1.2mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.

Frequency Parameters

- Frequency: 3.0MHz to 80.0MHz
- Frequency Stability: $\pm 30.00\text{ppm}$ to $\pm 100.00\text{ppm}$
- Ageing: $\pm 5\text{ppm max/yr @ } 25^\circ\text{C}$

Electrical Parameters

- Supply Voltage: $3.3\text{V} \pm 10\%$

Operating Temperature Ranges

- 20 to 70°C
- 40 to 85°C

Output Details

- Output Compatibility: CMOS
- Drive Capability: 15pF max
- Output Voltage Low (V_{ol}): 10%V_s max
- Output Voltage High (V_{oh}): 90%V_s min

Output Control

- Standby Operation:
 - Logic '1' ($\geq 70\%V_s$) to pad 1 enables oscillator output.
 - Logic '0' ($\leq 30\%V_s$) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state.
 - No connection to pad 1 enables oscillator output.
- Standby Current: 10 μA max

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Shock: IEC 60068-2-27: 1000g, 1ms, 3 times in each of 3 mutually perpendicular planes.
- Vibration: IEC 60068-2-6: 1.5mm amplitude, 10Hz-55Hz, 1min in 3 mutually perpendicular planes, duration 2hrs each plane (total 6hrs).

Ordering Information

- Frequency*
- Model*
- Output
- Frequency Stability*
- Operating Temperature Range*
- Supply Voltage
- (*minimum required)
- Example
 - 10.0MHz IQXO-640
 - CMOS $\pm 50\text{ppm}$ -20 to 70°C 3.3V


Compliance

- RoHS Status (2015/863/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details


- Pack Style: Reel: Tape & reel in accordance with EIA-481-D
- Pack Size: 3,000
- Pack Style: Cutt: Cut tape
- Pack Size: 100

Outline (mm)




- Pad Connections
- Standby Operation
 - GND
 - Output
 - +V_s

Solder Pad Layout




Test Circuit



* Inclusive of jigging and equipment capacitance

Wave Form





ISSUE 4; October 2021

Electrical Specification - maximum limiting values 3.3V \pm 10%

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Current Draw	Rise and Fall Time (10-90%)	Duty Cycle
		°C	ppm	mA	ns	%
3.0MHz	20.0MHz	-20 to 70	\pm 30.0	4	4.5	45/55%
		-40 to 85	\pm 50.0	4	4.5	45/55%
20.000001MHz	40.0MHz	-20 to 70	\pm 30.0	6	4.5	45/55%
		-40 to 85	\pm 50.0	6	4.5	45/55%
40.000001MHz	60.0MHz	-20 to 70	\pm 30.0	8	4.5	45/55%
		-40 to 85	\pm 50.0	8	4.5	45/55%
60.000001MHz	80.0MHz	-20 to 70	\pm 30.0	10	4.5	45/55%
		-40 to 85	\pm 50.0	10	4.5	45/55%

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

ISSUE 4; October 2021

Description

- Standard 1.6 x 1.2mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.

Frequency Parameters

- Frequency: 3.0MHz to 80.0MHz
- Frequency Stability: $\pm 30.00\text{ppm}$ to $\pm 100.00\text{ppm}$
- Ageing: $\pm 5\text{ppm max/yr @ } 25^\circ\text{C}$

Electrical Parameters

- Supply Voltage: $2.5\text{V} \pm 10\%$

Operating Temperature Ranges

- 20 to 70°C
- 40 to 85°C

Output Details

- Output Compatibility: CMOS
- Drive Capability: 15pF max
- Output Voltage Low (V_{ol}): 10%V_s max
- Output Voltage High (V_{oh}): 90%V_s min

Output Control

- Standby Operation:
 - Logic '1' ($\geq 70\%V_s$) to pad 1 enables oscillator output.
 - Logic '0' ($\leq 30\%V_s$) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state.
 - No connection to pad 1 enables oscillator output.
- Standby Current: 10 μA max

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Shock: IEC 60068-2-27: 1000g, 1ms, 3 times in each of 3 mutually perpendicular planes.
- Vibration: IEC 60068-2-6: 1.5mm amplitude, 10Hz-55Hz, 1min in 3 mutually perpendicular planes, duration 2hrs each plane (total 6hrs).

Ordering Information

- Frequency*
- Model*
- Output
- Frequency Stability*
- Operating Temperature Range*
- Supply Voltage
- (*minimum required)
- Example
 - 10.0MHz IQXO-641
 - CMOS $\pm 50\text{ppm}$ -20 to 70°C 2.5V


Compliance

- RoHS Status (2015/863/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Reel: Tape & reel in accordance with EIA-481-D
- Pack Size: 3,000
- Pack Style: Cutt: Cut tape
- Pack Size: 100


Outline (mm)




Pad Connections

- Standby Operation
- GND
- Output
- +Vs

Solder Pad Layout




Test Circuit



* Inclusive of jigging and equipment capacitance

Wave Form





ISSUE 4; October 2021

Electrical Specification - maximum limiting values 2.5V \pm 10%

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Current Draw	Rise and Fall Time	Duty Cycle
		°C	ppm	mA	ns	%
3.0MHz	20.0MHz	-20 to 70	\pm 30.0	3	4.5	45/55%
		-40 to 85	\pm 50.0	3	4.5	45/55%
20.000001MHz	40.0MHz	-20 to 70	\pm 30.0	5	4.5	45/55%
		-40 to 85	\pm 50.0	5	4.5	45/55%
40.000001MHz	60.0MHz	-20 to 70	\pm 30.0	7	4.5	45/55%
		-40 to 85	\pm 50.0	7	4.5	45/55%
60.000001MHz	80.0MHz	-20 to 70	\pm 30.0	9	4.5	45/55%
		-40 to 85	\pm 50.0	9	4.5	45/55%

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

ISSUE 4; October 2021

Description

- Standard 1.6 x 1.2mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.

Frequency Parameters

- Frequency: 3.0MHz to 80.0MHz
- Frequency Stability: $\pm 30.00\text{ppm}$ to $\pm 100.00\text{ppm}$
- Ageing: $\pm 5\text{ppm max/yr @ } 25^\circ\text{C}$

Electrical Parameters

- Supply Voltage: $1.8\text{V} \pm 10\%$

Operating Temperature Ranges

- 20 to 70°C
- 40 to 85°C

Output Details

- Output Compatibility: CMOS
- Drive Capability: 15pF max
- Output Voltage Low (V_{ol}): 10%V_s max
- Output Voltage High (V_{oh}): 90%V_s min

Output Control

- Standby Operation:
 - Logic '1' ($\geq 70\%V_s$) to pad 1 enables oscillator output.
 - Logic '0' ($\leq 30\%V_s$) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state.
 - No connection to pad 1 enables oscillator output.
- Standby Current: 10 μA max

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Shock: IEC 60068-2-27: 1000g, 1ms, 3 times in each of 3 mutually perpendicular planes.
- Vibration: IEC 60068-2-6: 1.5mm amplitude, 10Hz-55Hz, 1min in 3 mutually perpendicular planes, duration 2hrs each plane (total 6hrs).

Ordering Information

- Frequency*
- Model*
- Output
- Frequency Stability*
- Operating Temperature Range*
- Supply Voltage
- (*minimum required)
- Example
 - 10.0MHz IQXO-642
 - CMOS $\pm 50\text{ppm}$ -20 to 70°C 1.8V


Compliance

- RoHS Status (2015/863/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details


- Pack Style: Cutt: Cut tape
- Pack Size: 100
- Pack Style: Reel: Tape & reel in accordance with EIA-481-D
- Pack Size: 3,000

Outline (mm)




- Pad Connections
- Standby Operation
 - GND
 - Output
 - +V_s

Solder Pad Layout




Test Circuit



* Inclusive of jigging and equipment capacitance

Wave Form



ISSUE 4; October 2021

Electrical Specification - maximum limiting values 1.8V \pm 10%

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Current Draw	Rise and Fall Time	Duty Cycle
		°C	ppm	mA	ns	%
3.0MHz	20.0MHz	-20 to 70	\pm 30.0	3	4.5	45/55%
		-40 to 85	\pm 50.0	3	4.5	45/55%
20.000001MHz	40.0MHz	-20 to 70	\pm 30.0	4	4.5	45/55%
		-40 to 85	\pm 50.0	4	4.5	45/55%
40.000001MHz	60.0MHz	-20 to 70	\pm 30.0	5	4.5	45/55%
		-40 to 85	\pm 50.0	5	4.5	45/55%
60.000001MHz	80.0MHz	-20 to 70	\pm 30.0	7	4.5	45/55%
		-40 to 85	\pm 50.0	7	4.5	45/55%

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: 0800 1808 443

France: 0800 901 383

USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com