

## knurl cutter HSSE-PM 90°

For use on knurl cutter tools 19100



### Application:

For producing knurls in accordance with DIN 82 RGE 30° (in holders with 2 knurls) and RBL30° or RBR30° (in holders with 1 knurl) in the steel, stainless steel, non-ferrous metals and cast iron material groups.

### Execution:

- HSSE PM 90°, ground tooth flanks, uncoated

### Advantage:

- High precision with ground teeth and good cutting performance, even with difficult materials
- Very good surface quality and long service life with high-quality HSSE-PM cutting material



<b>Art. no.</b>	<b>19165 010</b>
<b>Brand</b>	QUICK
<b>Manufacturer Part Number</b>	42000187
<b>Knurling wheel diameter</b>	8.9 mm
<b>Partition</b>	1 mm
<b>Surface</b>	Uncoated
<b>Gross Weight</b>	0.002 kg
<b>Product Group</b>	192