

Weldon surface chucks

In accordance with ISO 7388-1 (DIN 69871)

ORION[®]

Application:

For clamping tools with straight shanks and clamping surfaces in line with DIN 1835 B.

Execution:

- All tapers and tolerances are precision-ground.
- Taper tolerance AT3.
- Strength HRC 57-60.
- Core strength 1,000-1,200 N/mm².
- With Balluff chip hole.

Advantage:

- Prevents the tool from slipping while maintaining high concentricity.

Delivery:

1x surface chuck (Weldon) in accordance with ISO 7388-1 (DIN 69871).



Art. no.	23157 025
Brand	ORION
Manufacturer Part Number	23157025
Tool holding device	SK 40
Clamping diameter	25 mm
Projecting length	100 mm
Outer diameter	65 mm
Length 2	24 mm
Length 3	25 mm
Balancing quality	G 6.3 at 15 rpm
Form	AD/AF
Thread dimension	M18 x 2
Gross Weight	2.432 kg
Product Group	2AV

EAN

4053625290949