

Machine accessory cabinet with hinged doors, height 1000 mm

With drawers and shelves, load capacity 40/50 kg

Application:

For secure and clearly-arranged storage of tools, accessories and other parts.

Execution:

- Cabinet housing made of sheet steel with 3-sided anti-roll-off edging, 25 mm high
- Shelves galvanised, height-adjustable
- Doors with grip handles, lockable with cylinder security lock, incl. 2 keys



Art. no.	50132 005
Brand	HK
Manufacturer Part Number	50132005
Door design	Full-sheet panel
Width	1000 mm
Depth	500 mm
Height	1000 mm
Number of shelves	2 PCS
Shelf width	925 mm
Shelf depth	430 mm
Load-carrying capacity per shelf	50 kg
Number of drawers	2 PCS
Drawer front height	2 x 90 mm
Drawer width (inner dimension)	380 mm
Drawer depth (inner dimension)	445 mm
Load-carrying capacity per drawer	40 kg
Pullout type	Full extension
With partition wall	No
Load-carrying capacity	200 kg
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Cabinet colour	Light grey RAL 7035
Gross Weight	60.000 kg
Product Group	504

EAN

4053625402168