

## Hydraulic hand pumps

For double-acting cylinders



### Application:

For operating hydraulic cylinders.

### Execution:

- The piston hand pumps comprise a pump unit, drain valve and oil reservoir.
- The pumps can be used with the pump head downwards both horizontally and vertically.
- Ready for operation with oil filling
- Dual-acting cylinder.

### Advantage:

- Automatic switch-over from low pressure to high pressure range in two-stage pumps.

### Delivery:

1x ENERPAC hydraulic hand pump P 84.



<b>Art. no.</b>	<b>29701 090</b>
<b>Brand</b>	ENERPAC
<b>Manufacturer Part Number</b>	P84
<b>Model</b>	P-84
<b>Number of steps</b>	2
<b>Max. operating pressure 1. Level</b>	34 bar
<b>Max. operating pressure 2. Level</b>	700 bar
<b>Feed volume per stroke</b>	16.39 cm <sup>3</sup>
<b>Feed volume per stroke 2</b>	2.46 cm <sup>3</sup>
<b>Usable oil volume</b>	2200 cm <sup>3</sup>
<b>Connection thread</b>	NPT 3/8 inch
<b>Weight</b>	11.8 kg
<b>Gross Weight</b>	14.300 kg
<b>Product Group</b>	258