



- Unit purifies air at up to 8 workplaces
- The Constant Flow Control (CFC) guarantees optimal air flow regulation for each working place independent of the connected workplaces
- Efficiency test via USB port
- Electronic filter control with optical and acoustical filter alarm
- 4 wheels to allow easy movement of the unit
- Remote control via RS 232 port
- Low noise level
- The fume extraction system Zero Smog 6V (ZS 6V) is user-friendly with quick and simple installation and filter exchange. It has a low noise emission level and is small and convenient to locate within the work area. The high quality components used in the ZS 6V result in low servicing requirements and long system life. To increase filter lifetime and save on energy, the ZS 6V is fitted with an constant flow control (CFC) – depending on the number of connected workplaces. To extend the capacity an external pre-filter can be fixed directly to the ZS 6V. The powerful maintenance.

Zero Smog 6V

Code No.: T0053666699

Dimensions W x D x H (mm)	460 x 460 x 665
Dimensions W x D x H (Inch)	18,11 x 18,11 x 26,18
Weight (ca) in kg	40
Voltage	230 V, 50/60 Hz
Heating output	460 VA
Noise level (distance 1 m) dB(A)	
Max. vacuum	---
Capacity m ³ /h	615
Pre filter	Pre filter mat class F7
Cartridge Volume Extraction	Particle filter H13, Wide band gas filter (50 % Active carbon / 50 % Chemisorb)
Max. capacity	1-8 workplaces
Interface RS232 (Remote control)	All system functions can be operated and remotely monitored via the RS232 port.
USB interface	on
WX compatible	on

Weller Tools GmbH
Carl-Benz-Straße 2
74354 Besigheim
Germany

Phone: +49 (0) 7143 / 580-0
Fax.: +49 (0) 7143 / 580-108
Email: info@weller-tools.com
Web: www.weller-tools.com