

## Cemented carbide milling bit set, 5 piece

Shank diameter 6 mm, with TiAlN coating

**ATORN®**

### Application

For deburring and finishing work on cast parts, roughly machined workpieces or welding seams - can be used in hand-guided or on stationary machines.

### Version

- For use with cast iron, unhardened steel, tool steel and alloyed stainless steel
- Cutting speed: 450-900 m/min
- Precise spindle bearing with high concentricity required

### Advantage

- With TiAlN coating for longer service life, strength and effective manufacture

### Delivery

1x ZYA-S 1020, WRC 1225, RBF 1225, SPG 1020, KEL 1228 each, in plastic box



<b>Art. no.</b>	<b>76006 920</b>
<b>Shaft diameter</b>	6 mm
<b>Serration type</b>	6
<b>Number of pieces in assortment/set</b>	5 PCS

### EAN-Code

4050293175578