

Crimp Information Sheet

Terminal Part Number: 12089040
 Surface Plating: SN
 Material Thickness [mm]: 0,32
 Cross Section [mm²]: 0,50 | 0,80

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*


Cable Type codes: 1002
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,60 - 2,18
 Seal(s): 15324985

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1002 0,50 / 15324985		1,78	80	1,10	0,05	2,40	0,10	4,30	0,10	4,40	0,10
1002 0,80 / 15324985		2,02	90	1,15	0,05	2,45	0,10	4,50	0,10	4,50	0,10

Cable type code legend:

1002:

Industry Designator: SAE
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: ECTFE, ETFE, PBT, PTFE, PUR, TFE
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 12089040
 Surface Plating: SN
 Material Thickness [mm]: 0,32
 Cross Section [mm²]: 0,50 | 0,80

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 1002
 Crimp Process: (T) CRIMP ONLY - CORE IS DIP SOLDERED, THEN CRIMPED
 Insulation Range Φ [mm]: 1,60 - 2,18
 Seal(s): 15324985

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1002 0,50 / 15324985		1,78	80	1,10	0,05	2,40	0,10	4,30	0,10	4,40	0,10
1002 0,80 / 15324985		2,02	90	1,15	0,05	2,45	0,10	4,50	0,10	4,50	0,10

Cable type code legend:

1002:

Industry Designator: SAE
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: ECTFE, ETFE, PBT, PTFE, PUR, TFE
 Insul. Wall Designator: THIN

