

## ES EPG 60 AEH 185

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



### Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

### General ordering data

|            |                            |
|------------|----------------------------|
| Type       | ES EPG 60 AEH 185          |
| Order No.  | <a href="#">2577930000</a> |
| Version    | Crimping tool insert       |
| GTIN (EAN) | 4050118590654              |
| Qty.       | 1 pc(s).                   |

**Data sheet**

**ES EPG 60 AEH 185**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 25 g

**Crimp inserts**

|                            |       |                      |    |
|----------------------------|-------|----------------------|----|
| Crimp cross-section copper | 185   | Crimping width in mm | 22 |
| Crimping width             | 22 mm |                      |    |

**Description of contact**

Type of contact Wire-end ferrules with/  
without plastic collars

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC000168    | ETIM 6.0   | EC001282    |
| eClass 6.2 | 21-04-38-11 | eClass 9.0 | 21-04-90-90 |
| eClass 9.1 | 21-01-90-90 |            |             |