

BONDLOCTM

FORMULAS THAT WORK

SAFETY DATA SHEET

B641

According to Regulation (EC) No 1907/2006, Annex II, as amended by Regulation (EU) No 453/2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name B641
Container size 10ml, 25ml, 50ml and 250ml bottles

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Adhesive.

1.3. Details of the supplier of the safety data sheet

Supplier

Bondloc UK Ltd
Unit 2 Bewdley Business Park
Long Bank
Bewdley
Worcestershire
DY12 2TZ
+44 (0)1299 269269
+44 (0)1299 269210
sales@bondloc.co.uk

1.4. Emergency telephone number

Emergency telephone +44 (0)1299 269269

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified
Health hazards Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Skin Sens. 1 - H317 STOT SE 3 - H335 STOT SE 3 - H335 STOT SE 3 - H335
Environmental hazards Not Classified

2.2. Label elements

Pictogram



Signal word Warning

Hazard statements H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

B641

Precautionary statements	<p>P261 Avoid breathing vapour/ spray.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P271 Use only outdoors or in a well-ventilated area.</p> <p>P272 Contaminated work clothing should not be allowed out of the workplace.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P302+P352 IF ON SKIN: Wash with plenty of water.</p> <p>P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.</p> <p>P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P312 Call a POISON CENTER/ doctor if you feel unwell.</p> <p>P321 Specific treatment (see medical advice on this label).</p> <p>P332+P313 If skin irritation occurs: Get medical advice/ attention.</p> <p>P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.</p> <p>P337+P313 If eye irritation persists: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p> <p>P403+P233 Store in a well-ventilated place. Keep container tightly closed.</p> <p>P405 Store locked up.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>
Contains	Ethoxylated Bisphenol A Dimethacrylate, 2-hydroxypropyl methacrylate, α,α -dimethylbenzyl hydroperoxide, maleic acid, 1-Acetyl-2-phenylhydrazine

2.3. Other hazards**SECTION 3: Composition/information on ingredients****3.2. Mixtures**

Ethoxylated Bisphenol A Dimethacrylate	30-60%
CAS number: 41637-38-1	
Classification	
Skin Irrit. 2 - H315	
Eye Irrit. 2 - H319	
Skin Sens. 1 - H317	
STOT SE 3 - H335	
2-hydroxypropyl methacrylate	10-30%
CAS number: 923-26-2 EC number: 213-090-3	
Classification	
Eye Irrit. 2 - H319	
Skin Sens. 1 - H317	

B641

α,α-dimethylbenzyl hydroperoxide	1-5%
CAS number: 80-15-9	EC number: 201-254-7
Classification	
Org. Perox. E - H242	
Acute Tox. 4 - H302	
Acute Tox. 4 - H312	
Acute Tox. 3 - H331	
Skin Corr. 1B - H314	
Eye Dam. 1 - H318	
STOT SE 3 - H335	
STOT RE 2 - H373	
Aquatic Chronic 2 - H411	
maleic acid	<1%
CAS number: 110-16-7	EC number: 203-742-5
Classification	
Acute Tox. 4 - H302	
Skin Irrit. 2 - H315	
Eye Irrit. 2 - H319	
Skin Sens. 1 - H317	
STOT SE 3 - H335	
1-Acetyl-2-phenylhydrazine	<1%
CAS number: 114-83-0	
Classification	
Acute Tox. 3 - H301	
Skin Irrit. 2 - H315	
Eye Irrit. 2 - H319	
Skin Sens. 1 - H317	
STOT SE 3 - H335	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Move affected person to fresh air at once. Get medical attention if any discomfort continues.
Ingestion	Rinse mouth thoroughly with water. Give plenty of water to drink. Do not induce vomiting.
Skin contact	Wash skin thoroughly with soap and water. Get medical attention.
Eye contact	Rinse immediately with plenty of water. Get medical attention if symptoms are severe or persist. Continue to rinse for at least 10 minutes.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact	Redness.
Eye contact	Conjunctivitis, irritation, tearing.

4.3. Indication of any immediate medical attention and special treatment needed

B641

Notes for the doctor Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with the following media: Carbon dioxide (CO₂). Foam. Alcohol-resistant foam. Water spray.

Unsuitable extinguishing media None known.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products Oxides of carbon. Oxides of nitrogen. Sulphur.

5.3. Advice for firefighters

Protective actions during firefighting Containers close to fire should be removed or cooled with water.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with skin and eyes. Provide adequate ventilation.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Absorb spillage with sand or other inert absorbent. Collect and place in suitable waste disposal containers and seal securely.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Use only in well-ventilated areas. Do not eat, drink or smoke when using this product. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store at temperatures between 8°C and 21°C. Store in tightly-closed, original container in a well-ventilated place.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Eye/face protection Wear eye protection.

B641

Hand protection	To protect hands from chemicals, gloves should comply with European Standard EN374.
Other skin and body protection	Wear apron or protective clothing in case of contact.
Respiratory protection	If ventilation is inadequate, suitable respiratory protection must be worn.

SECTION 9: Physical and Chemical Properties**9.1. Information on basic physical and chemical properties**

Appearance	Liquid.
Colour	Yellow.
Odour	Sweetish.
Odour threshold	Not available.
pH	pH (concentrated solution): 3-5
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	> 100°C
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not applicable.
Vapour pressure	-0.1 mm Hg @ 20°C
Vapour density	Not available.
Relative density	~ 1.08
Solubility(ies)	Slightly soluble in water.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	400-800 cps @ °C
Explosive properties	Not available.
Oxidising properties	Not available.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reactivity	Strong acids. Strong oxidising agents.
-------------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended.
------------------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Under normal conditions of storage and use, no hazardous reactions will occur.
---	--

B641**10.4. Conditions to avoid**

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid None known.

10.6. Hazardous decomposition products

Hazardous decomposition products In case of fire Other toxic gases and vapours

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute toxicity - oral**

ATE oral (mg/kg) 12,591.96791197

Acute toxicity - dermal

ATE dermal (mg/kg) 110,000.0

Acute toxicity - inhalation

ATE inhalation (vapours mg/l) 300.0

Inhalation Irritating to respiratory system.

Ingestion May cause irritation.

Skin contact Irritating.

Eye contact Risk of serious damage to eyes.

SECTION 12: Ecological Information

Ecotoxicity There are no data on the ecotoxicity of this product.

12.1. Toxicity**Ecotoxicity**

Toxicity Do not empty into drains/surface water/ground water

12.2. Persistence and degradability

Persistence and degradability There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not available.

12.4. Mobility in soil

Mobility Not considered mobile.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects Not available.

B641**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

General information	Dispose of waste product or used containers in accordance with local regulations
Disposal methods	Dispose of waste product or used containers in accordance with local regulations
Waste class	08 04 09 waste adhesives and sealants containing organic solvents or other dangerous substances.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78
and the IBC Code**

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

EU legislation Regulation (EC) No 1907/2006 of the European Parliament and of the council of 18 December 2006 concerning the Registration, evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labeling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

B641

Revision date	27/10/2014
SDS number	4632
Hazard statements in full	H242 Heating may cause a fire. H301 Toxic if swallowed. H302 Harmful if swallowed. H312 Harmful in contact with skin. H314 Causes severe skin burns and eye damage. H315 Causes skin irritation. H317 May cause an allergic skin reaction. H318 Causes serious eye damage. H319 Causes serious eye irritation. H331 Toxic if inhaled. H335 May cause respiratory irritation. H373 May cause damage to organs through prolonged or repeated exposure. H411 Toxic to aquatic life with long lasting effects.

PRECAUTIONS: This product and the auxiliary materials normally combined with it are capable of producing adverse health effects ranging from minor skin irritation to serious systemic effects. None of these materials should be used, stored, or transported until the handling precautions and recommendations as stated in the Material Safety Data Sheets (MSDS) for this and all other products being used are understood by all persons who will work with the product.

WARRANTY: All products purchased from or supplied by Bondloc are subject to terms and conditions set out in the contract. Bondloc warrants only that its product will meet those specifications designated as such herein or in other publications. All other information supplied by Bondloc is considered accurate but are furnished upon the express condition the customer shall make its own assessment to determine the product's suitability for a particular purpose. Bondloc makes no other warranty, either express or implied, including those regarding such other information, the data upon which the same is based, or the results to be obtained from the use thereof; that any product shall be merchantable or fit for any particular purpose; or that the use of such other information or product will not infringe any patent.