

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

SECTION 1: Identification of the substance/mixture and of the company/undertaking***1.1 Product identifier**

***Trade name:** S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

***Article number:** REVISC-S20

***CAS Number:**
8042-47-5

***EC number:**
232-455-8

***UFI:** AFU2-60AE-5009-57N3

***1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.

***Application of the substance / the mixture** Laboratory Chemicals

***1.3 Details of the supplier of the safety data sheet**

***Manufacturer/Supplier:**
Reagecon Diagnostics Ltd.
Shannon Free Zone,
Shannon,
Co. Clare,
Ireland.
Tel +353 61 472622
Fax +353 61 472642

***Further information obtainable by contacting:** sds@reagecon.ie

***1.4 Emergency telephone number:**

National Poisons Information Centre: +353 (1) 809 2166 (8.00 a.m. to 10.00 p.m. 7 days a week)
Healthcare Professionals: +353 (1) 809 2566 (24 hour service)

For Hazardous Materials [or Dangerous Goods] Incident

Spill, Leak, Fire, Exposure, or Accident

Call CHEMTREC

For Ireland call +(353)-19014670

For Outside Ireland call +1 703-741-5970 / 1-800-424-9300 CCN849800

SECTION 2: Hazards identification***2.1 Classification of the substance or mixture**

***Classification according to Regulation (EC) No 1272/2008**

The substance is not classified, according to the CLP regulation.

***2.2 Label elements**

***Labelling according to Regulation (EC) No 1272/2008** Void

***Hazard pictograms** Void

***Signal word** Void

***Hazard statements** Void

***2.3 Other hazards**

***Results of PBT and vPvB assessment**

***PBT:** Not applicable.

***vPvB:** Not applicable.

UL

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

(Contd. of page 1)

SECTION 3: Composition/information on ingredients

3.1 Substances**CAS No. Description**

CAS: 8042-47-5 White mineral oil, petroleum

Identification number(s)**EC number:** 232-455-8

SECTION 4: First aid measures

4.1 Description of first aid measures**General information:**

Immediately remove any clothing soiled by the product.
No special measures required.

***After inhalation:**

Provide fresh air, warmth and rest. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Obtain medical attention if any discomfort continues.

After skin contact:** Immediately rinse with water.After eye contact:**

Promptly wash eyes with plenty of water for up to 15 minutes. Open eyes wide apart and rinse well to remove any contact lenses. Do not remove contact lenses by hand. Get medical attention. Continue to rinse.

After swallowing:** If symptoms persist consult doctor.4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.***4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media**Suitable extinguishing agents:**

Indications shall be given whether any extinguishing media are inappropriate for a particular situation involving the substance or mixture

Use fire extinguishing methods suitable to surrounding conditions.

5.2 Special hazards arising from the substance or mixture** No further relevant information available.5.3 Advice for firefighters*****Protective equipment:**

Fire fighters should wear complete protective clothing including self-contained breathing apparatus. Do not breathe fumes. Keep containers cool by spraying with water if exposed to fire. Avoid run off to waterways and sewers

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures** Not required.6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.***6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Ensure adequate ventilation.

***6.4 Reference to other sections**

See Section 7 for information on safe handling.

(Contd. on page 3)

UL

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

(Contd. of page 2)

SECTION 7: Handling and storage

***7.1 Precautions for safe handling**

No special measures required.
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
Prevent formation of aerosols.

***Information about fire - and explosion protection:** Keep respiratory protective device available.

7.2 Conditions for safe storage, including any incompatibilities**Storage:**

***Requirements to be met by storerooms and receptacles:** No special requirements.

***Information about storage in one common storage facility:** Not required.

***Further information about storage conditions:** Keep receptacle tightly sealed.

***7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

***8.1 Control parameters**

***Ingredients with limit values that require monitoring at the workplace:** Not required.

***Additional information:** The lists valid during the making were used as basis.

***8.2 Exposure controls**

***Appropriate engineering controls** No further data; see section 7.

***Individual protection measures, such as personal protective equipment**

***General protective and hygienic measures:**

Immediately remove all soiled and contaminated clothing
Store protective clothing separately.
Do not inhale gases / fumes / aerosols.

***Respiratory protection:**

Not required.

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

***Hand protection**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Always ensure that gloves are inspected before use.

Selection of protective gloves must include consideration of the penetration times along with rates of diffusion and degradation. The selected glove should comply with the specifications of EU Directive 89/686/EEC and the standard EN374 derived from it.

***Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

(Contd. of page 3)

***Penetration time of glove material**

In the absence of data above, the exact break through time has to be sourced from the manufacturer of the protective gloves and has to be observed.

***Eye/face protection**

Goggles recommended during refilling: Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties**General Information**

*Physical state	Liquid
*Colour:	Colourless
*Odour:	Characteristic
*Odour threshold:	Not determined.
*Melting point/freezing point:	Undetermined.
*Boiling point or initial boiling point and boiling range	>260 °C
*Flammability	Not applicable.
*Lower and upper explosion limit	
*Lower:	Not determined.
*Upper:	Not determined.
*Flash point:	>112 °C
*Decomposition temperature:	Not determined.
*pH	Not determined.
*Viscosity:	
*Kinematic viscosity	Not determined.
*Dynamic:	Not determined.
*Solubility	
*water:	Not miscible or difficult to mix.
*Partition coefficient n-octanol/water (log value)	Not determined.
*Vapour pressure:	Not determined.
*Density and/or relative density	
*Density:	Not determined.
*Relative density	Not determined.
*Vapour density	Not determined.

***9.2 Other information**

*Appearance:	
*Form:	Liquid
*Important information on protection of health and environment, and on safety.	
*Ignition temperature:	Not determined.
*Explosive properties:	Product does not present an explosion hazard.
*Change in condition	
*Evaporation rate	Not determined.

***Information with regard to physical hazard classes**

*Explosives	Void
*Flammable gases	Void

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

(Contd. of page 4)

*Aerosols	Void
*Oxidising gases	Void
*Gases under pressure	Void
*Flammable liquids	Void
*Flammable solids	Void
*Self-reactive substances and mixtures	Void
*Pyrophoric liquids	Void
*Pyrophoric solids	Void
*Self-heating substances and mixtures	Void
*Substances and mixtures, which emit flammable gases in contact with water	Void
*Oxidising liquids	Void
*Oxidising solids	Void
*Organic peroxides	Void
*Corrosive to metals	Void
*Desensitised explosives	Void

SECTION 10: Stability and reactivity

- *10.1 Reactivity No further relevant information available.
- *10.2 Chemical stability
- *Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- *10.3 Possibility of hazardous reactions No dangerous reactions known.
- *10.4 Conditions to avoid No further relevant information available.
- *10.5 Incompatible materials: No further relevant information available.
- *10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- *11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008
- *Acute toxicity Based on available data, the classification criteria are not met.
- *Skin corrosion/irritation Based on available data, the classification criteria are not met.
- *Serious eye damage/irritation Based on available data, the classification criteria are not met.
- *Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- *Germ cell mutagenicity Based on available data, the classification criteria are not met.
- *Carcinogenicity Based on available data, the classification criteria are not met.
- *Reproductive toxicity Based on available data, the classification criteria are not met.
- *STOT-single exposure Based on available data, the classification criteria are not met.
- *STOT-repeated exposure Based on available data, the classification criteria are not met.
- *Aspiration hazard Based on available data, the classification criteria are not met.
- *11.2 Information on other hazards

*Endocrine disrupting properties

Substance is not listed.

SECTION 12: Ecological information

- *12.1 Toxicity
- *Aquatic toxicity: No further relevant information available.

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

(Contd. of page 5)

***12.2 Persistence and degradability** No further relevant information available.

***12.3 Bioaccumulative potential** No further relevant information available.

***12.4 Mobility in soil** No further relevant information available.

***12.5 Results of PBT and vPvB assessment**

***PBT:** Not applicable.

***vPvB:** Not applicable.

***12.6 Endocrine disrupting properties**

The product does not contain substances with endocrine disrupting properties.

***12.7 Other adverse effects**

***Additional ecological information:**

***General notes:**

Water hazard class 1 (German Regulation) (Assessment by list): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

SECTION 13: Disposal considerations

***13.1 Waste treatment methods**

***Recommendation** Smaller quantities can be disposed of with household waste.

***Uncleaned packaging:**

***Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

*14.1 UN number or ID number *ADR, IMDG, IATA	Void
*14.2 UN proper shipping name *ADR, IMDG, IATA	Void
*14.3 Transport hazard class(es) *ADR, IMDG, IATA *Class	Void
*14.4 Packing group *ADR, IMDG, IATA	Void
*14.5 Environmental hazards: *Marine pollutant:	No
*14.6 Special precautions for user	Not applicable.
*14.7 Maritime transport in bulk according to IMO instruments	Not applicable.
*Transport/Additional information:	Not dangerous according to the above specifications.
*UN "Model Regulation":	Void

UL

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 07.02.2024

version number 2

Revision: 07.02.2024

**Trade name: S20 KINEMATIC VISCOSITY,
DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C**

(Contd. of page 6)

SECTION 15: Regulatory information

***15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

***Directive 2012/18/EU**

***Named dangerous substances - ANNEX I Substance is not listed.**

***DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**

Substance is not listed.

***REGULATION (EU) 2019/1148**

***Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))**

Substance is not listed.

***Annex II - REPORTABLE EXPLOSIVES PRECURSORS**

Substance is not listed.

***Regulation (EC) No 273/2004 on drug precursors**

Substance is not listed.

***Regulation (EC) No 111/2005 laying down rules for the monitoring of trade between the Community and third countries in drug precursors**

Substance is not listed.

***National regulations:**

***Waterhazard class: Water hazard class 1 (Assessment by list): slightly hazardous for water.**

***15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.**

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

***Department issuing SDS: Health and Safety**

***Contact: sds@reagecon.ie**

***Abbreviations and acronyms:**

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative