



### Model Number

NBB1,5-4M25-E2

### Features

- Basic series
- 1.5 mm flush

### Accessories

#### BF 4

Mounting flange, 4 mm

## Technical Data

### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	1.5 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 1.215 mm	
Reduction factor $r_{Al}$		0.46	
Reduction factor $r_{Cu}$		0.41	
Reduction factor $r_{304}$		0.89	
Reduction factor $r_{Brass}$		0.59	

### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V	
Switching frequency	$f$	0 ... 3000 Hz	
Hysteresis	$H$	1 ... 15 %	
Reverse polarity protection		reverse polarity protected	
Short-circuit protection		yes	
Voltage drop	$U_d$	≤ 3 V	
Operating current	$I_L$	0 ... 200 mA	
Off-state current	$I_r$	0 ... 0.1 mA typ. 0.1 μA at 25 °C	
No-load supply current	$I_0$	≤ 10 mA	
Switching state indicator		LED, yellow	

### Ambient conditions

Ambient temperature		-25 ... 70 °C (-13 ... 158 °F)
---------------------	--	--------------------------------

### Mechanical specifications

Connection type	cable PVC , 2 m
Core cross-section	0.14 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	POM
Protection degree	IP67


### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated ≤36 V

## Dimensions



## Electrical Connection

