



SIMATIC DP, ELECTRONIC MODULE F. ET 200S, 1 COUNT
 24V/100KHZ 15 MM WIDE, OPERATION MODES: COUNT,
 MEASURE, (PERIOD DURATION MEASUREMENT HIGH
 RESOLUTION) WITH CLOCK CYCLIC SYNCHRON.APP

Figure similar

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
from load voltage L+ (without load), max.	42 mA
from backplane bus 3.3 V DC, max.	10 mA
Encoder supply	
24 V encoder supply	
• 24 V	Yes; L+ (-0.8 V)
• short-circuit protection	Yes
• Output current, max.	500 mA
Power losses	
Power loss, typ.	1 W
Hardware configuration	
Module exchange	
• Hot swapping the IM-DP	Yes
• Module exchange under process voltage	Yes
Digital inputs	
Number of digital inputs	1
Functions	Gate control, synchronization, latch function

Input characteristic curve in accordance with IEC 61131, type 2	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5V
• for signal "1"	+11 to +30V
Input current	
• for signal "0", max. (permissible quiescent current)	2 mA
• for signal "1", typ.	9 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	2.5 µs; Filter off: 2.5 µs (200 kHz), filter on: 25 µs (20 kHz)
Cable length	
• shielded, max.	100 m; Filter 20 kHz: 100 m, filter 200 kHz: 50 m
Digital outputs	
Number of digital outputs	1
short-circuit protection	Yes
• Response threshold, typ.	2.6 A to 4 A
Limitation of inductive shutdown voltage to	L+ (-50 to -60 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• on lamp load, max.	5 W
Output voltage	
• Rated value (DC)	24 V
• for signal "0", max.	3 V
• for signal "1", min.	L+ (-1 V)
Output current	
• for signal "1" permissible range for 0 to 40 °C, min.	5 mA
• for signal "1" permissible range for 0 to 40 °C, max.	2 000 mA
• for signal "1" permissible range for 0 to 60 °C, min.	5 mA
• for signal "1" permissible range for 0 to 60 °C, max.	500 mA; 1000 mA at 50 °C
• for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
• "0" to "1", max.	100 µs
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz

Cable length	
• shielded, max.	1 000 m
• Unshielded, max.	600 m

Encoder	
Number of connectable encoders, max.	1

Connectable encoders	
• Incremental encoder (asymmetrical)	Yes
• 24 V initiator	Yes
• 2-wire sensor	Yes

Interrupts/diagnostics/status information	
Diagnostic messages	
• Diagnostic functions	Yes
Diagnostics indication LED	
• Group error SF (red)	Yes
• Status indicator digital output (green)	Yes
• Status indicator digital input (green)	Yes
• Status indicator backward counting (green)	Yes
• Status indicator forward counting (green)	Yes

Integrated Functions	
Measuring functions	
Measuring range	
— Frequency measurement, min.	0.1 Hz
— Frequency measurement, max.	100 kHz
— Period measurement, min.	10 µs
— Period measurement, max.	120 s
— Velocity measurement, min.	1 1/min
— Velocity measurement, max.	25 000 1/min

Counter	
Number of counter inputs	1; 32 Bit
Minimum pulse width	2.5 µs; Filter off: 2.5 µs (200 kHz), filter on: 25 µs (20 kHz)

Parameter	
Remark	16 byte

Galvanic isolation	
Galvanic isolation digital inputs	
• Galvanic isolation digital inputs	No; only opposite shielding
Galvanic isolation counter	
• between the channels and the backplane bus	Yes
• between the channels and the load voltage L+	No

Dimensions	
------------	--

Width	15 mm
Height	81 mm
Depth	52 mm
Weights	
Weight, approx.	40 g
last modified:	12.03.2015