

Product information

78 71 125 ESD

Electronic Super Knips® ESD

DIN ISO 9654 DIN EN 61 340-5



- With lead catcher - no uncontrolled loss of cut wire ends
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Special tool steel, burnished
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter




General

Article No.	78 71 125 ESD
EAN	4003773025191
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	57 g
Dimensions	125 x 61 x 13 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.2 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm
ESD	yes



technical change and errors excepted

