

Tilting drum with roll-off mechanism—for heavy bulk materials

Carrying capacity 1500-3000 kg, without wheels

Application:

For the collection and disposal of all types of very heavy bulk goods and solid materials.

Execution:

- can be tilted at any height using a wire rope hoist from the forklift seat
- Sheet metal tray with surrounding edge profile
- sturdy base frame with fork pockets
- Protection against accidental slipping and tipping
- All dimensions without wheels
- **design with wheels:** see under Accessories order separate wheelset no. 50266 370 (for 0.30 m³l containers) or no. 50266 635 (for 0.50 – 2.00 m³l containers) in addition, design height 220 mm

Advantage:

- Robust design for heavy bulk goods

Delivery:

Available upon request: zinc-plated cover, can be opened on both sides

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 621
Volume	0.5 m ³
Length	1550 mm
Width	820 mm
Tipper edge height	950 mm
Height	1045 mm
Fork pocket clearance	225 mm
Fork pocket size (W x H)	200 x 80 mm
With drain valve	No
With stacker seat tilt function	Yes
With perforated sheet	No
Load-carrying capacity	2500 kg
Surface	Zinc plated
Gross Weight	178.000 kg
Product Group	5A1

EAN

4052462019171