





CorePro LEDtube 1500mm UO 31.5W 830 T8

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pack back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes

Light Technical		
Color Code	830 [CCT of 3000K]	
Beam Angle (Nom)	240 degree(s)	
Luminous Flux	3,320 lumen	
Color Designation	White (WH)	
Correlated Color Temperature (Nom)	3000 K	
Luminous Efficacy (rated) (Nom)	105 lm/W	
Color Consistency	<6	
Color rendering index (CRI)	80	
LLMF At End Of Nominal Lifetime (Nom)	70 %	

Flickering value (PstLM)	1				
Stroboscopic effect value (SVM)	0.9				
Photobiological safety according to EN 62471 RG0					
Operating and Electrical					
Line Frequency	50 to 60 Hz				
Input Frequency	50 to 60 Hz				
Power Consumption	31.5 W				
Lamp Current (Nom)	135 mA				
Wattage Equivalent	58 W				
Starting Time (Nom)	0.5 s				
Warm-up time to 60% light	0.5 s				
Power Factor (Fraction)	0.9				
Voltage (Nom)	220-240 V				
LED alternative to fluorescent lamp power	58 W				
Temperature					
Ambient temperature range	-20 to +45 °C				
T-Case Maximum (Nom)	55 °C				
Controls and Dimming					
Dimmable	No				
Mechanical and Housing					
Bulb Finish	Frosted				
Bulb Material	Glass				


Product Length	1,500 mm		
Bulb Shape	Tube, double-ended		
Approval and Application			
Energy Efficiency Class	F		
Energy Saving Product	Yes		
Approval Marks	RoHS compliance CE marking KEMA Keur		
	certificate		
Energy Consumption kWh/1000 h	32 kWh		
EPREL Registration Number	1384737		
Product Data			
Full product code	871951448652200		
Order product name	CorePro LEDtube 1500mm UO 31.5W 830		
	Т8		
Order code	929003577802		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	20		
Material Nr. (12NC)	929003577802		
Full product name	CorePro LEDtube 1500mm UO 31.5W 830		
	Т8		
EAN/UPC - Case	8719514486539		
EAN/UPC - Product/Case	8719514486522		


Dimensional drawing




Product	D1	D2	A1	A2	А3
CorePro LEDtube 1500mm UO	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
31.5W 830 T8					


Photometric data





Spectral Power Distribution Colour







Calculus Photometrics 1.5 Philips Lighting R.V. Page: 17

General uniform lighting - CorePro LEDtube 1500mm UO 31.5W 830 T8

Lifetime






Lumen Maintenance Diagram - CorePro LEDtube 1500mm UO 31.5W 830 T8

Life Expectancy Diagram

3

Lifetime



Life Expectancy Diagram



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.