SIEMENS

Data sheet 6GT2801-2BA10

product type designation



RF340R reader

SIMATIC RF300; Reader RF340R (GEN2); RS422 interface (3964R); IP67, -25 to +70 $^{\circ}$ C, 75x 75x 41 mm with integrated antenna .

suitability for operation	RF300, ISO 15693 and MOBY E transponder, for connecting to communication modules
radio frequencies	
operating frequency / rated value	13.56 MHz
range / maximum	140 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	RF300 specific, ISO 15693, ISO 18000-3, ISO 14443
transfer rate / with radio transmission / maximum	106 kbit/s
product feature / multitag-capable	No
electrical data	
transfer rate / at the point-to-point connection / serial / maximum	115.2 kbit/s
transmission time / for user data	
for write access / per byte / typical	0.13 ms
 for read access / per byte / typical 	0.13 ms
interfaces	
standard for interfaces / for communication	RS422
type of electrical connection	M12, 8-pin
mechanical data	
material	PA 12
color	Ti gray
tightening torque / of the screw for securing the equipment / maximum	1.5 N·m
mounting distance / relating to metal surfaces / recommended / minimum	0 mm
supply voltage, current consumption, power loss	
supply voltage	
at DC / rated value	24 V
• at DC	20.4 28.8 V
consumed current / at DC	
• at 24 V / typical	0.06 A
ambient conditions	
ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
during transport	-40 +85 °C
protection class IP	IP67
shock resistance	EN 60721-3-7 Class 7 M2
shock acceleration	500 m/s ²

vibrational acceleration	200 m/s²
design, dimensions and weights	
width	75 mm
height	41 mm
depth	75 mm
net weight	0.25 kg
fastening method	2 x M5 screws
wire length	
 for RS 422 interface / maximum 	1000 m
product features, product functions, product components / general	
display version	5-color LED
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	Radio acc. to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, cULus
certificate of suitability	
• IECEx	No
MTBF	260 y
further information / internet-Links	
Internet-Link	
 to web page: selection aid TIA Selection Tool 	https://support.industry.siemens.com/cs/ww/en/view/67384964
 to website: Industrial communication 	http://www.siemens.com/ident/rfid
to website: Industry Mall	https://mall.industry.siemens.com
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
to website: Image database	http://automation.siemens.com/bilddb
to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 12/18/2020 🖸