

DULUX[®] D/E

IMPROVED LIFE TIME & OSRAM SYSTEM +
GUARANTEE



DULUX[®] D/E



QTP-D/E 2x10-13



OSRAM System+ Guarantee


Benefits

- Extremely economical
- Good quality of light
- Excellent luminous flux
- Long service life time¹
- OSRAM System+ Guarantee LUMILUX® with OSRAM QUICKTRONIC® ECG
- Environmental friendly

Product Features

- Improved average lamp life: up to 20.000 h (with QUICKTRONIC®)
- Good color rendering index 1B (R_a 80...89)
- Improved lumen maintenance
- Dimmable from 3...100%
- For operation on electronic control gear (ECG)
- Available light colors: Cool Daylight (865), Cool White (840), White (835), Warm White (830), Extra Warm White (827)

Dimensions



Description	Base	Max Length L1 [mm]	Max Length L1 IEC [mm]	Max Length L2 [mm]
DULUX® D/E 10 W	G24q-1	87	95	103
DULUX® D/E 13 W	G24q-1	115	130	131
DULUX® D/E 18 W	G24q-2	130	140	146
DULUX® D/E 26 W	G24q-3	149	160	165

¹ Service life time is the mathematical life time (maintenance multiplied with the % of failed lamps e.g. B10) for lamps in an installation after which the installation luminous flux (100 h value) decreased by 30% (decrease in luminous flux and failed lamps) for indoor lighting

Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Electrical Data²

Lamps operated with **HF³** reference control gear at 25 °C (100 h aged) ambient temperature

DULUX® D/E	Lamp Voltage rated [V]	Lamp Current rated [mA]	Lamp Power rated [W]
10 W	51	190	9.5
13 W	77	165	12.5
18 W	80	210	16.5
26 W	80	300	24.0

Photometrical Data at 25 °C (100 h aged) ambient temperature⁴

DULUX® D/E	Light Color LUMILUX®	Color Rendering Index (CRI), Ra	Lumi-nance (LC ⁵ 840) [cd/cm ²]	Target Color Coordinate X	Target Color Coordinate Y	Nominal Luminous Flux [lm]	Efficacy 25 °C [lm/W]
10 W	827 INTERNA	80 ... 89	4.0	0.455	0.415	600	63
10 W	830 Warm White	80 ... 89	4.0	0.440	0.403	600	63
10 W	835 White	80 ... 89	4.0	0.409	0.394	600	63
10 W	840 Cool White	80 ... 89	4.0	0.380	0.380	600	63
13 W	827 INTERNA	80 ... 89	4.0	0.455	0.415	900	72
13 W	830 Warm White	80 ... 89	4.0	0.440	0.403	900	72
13 W	835 White	80 ... 89	4.0	0.409	0.394	900	72
13 W	840 Cool White	80 ... 89	4.0	0.380	0.380	900	72
18 W	827 INTERNA	80 ... 89	4.5	0.455	0.415	1200	73
18 W	830 Warm White	80 ... 89	4.5	0.440	0.403	1200	73
18 W	835 White	80 ... 89	4.5	0.409	0.394	1200	73
18 W	840 Cool White	80 ... 89	4.5	0.380	0.380	1200	73
18 W	865 Cool Daylight	80 ... 89	4.5	0.313	0.337	1140	73
26 W	827 INTERNA	80 ... 89	5.5	0.455	0.415	1800	75
26 W	830 Warm White	80 ... 89	5.5	0.440	0.403	1800	75
26 W	835 White	80 ... 89	5.5	0.409	0.394	1800	75
26 W	840 Cool White	80 ... 89	5.5	0.380	0.380	1800	75
26 W	865 Cool Daylight	80 ... 89	5.5	0.313	0.337	1710	75

² According to IEC 60901

³ High Frequency


⁴ Measurement in accordance with IEC 60901, annex C and the relevant annex on rated colour characteristics in IEC 60081.

⁵ Light Color

Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Relative Luminous Flux / Ambient Temperature



For more detailed information please refer to our technical guide – Compact Fluorescent Lamps. Free download at www.osram.com

Lifetime⁶

	ECG ⁷ preheated IEC switching cycle ⁸
B50⁹	20,000 h
Service life time¹⁰	13,000 h
LLMF¹¹ 2.000 h	0.90
LLMF 4.000 h	0.84
LLMF 6.000 h	0.82
LLMF 8.000 h	0.81
LLMF 12.000 h	0.78
LLMF 16.000 h	0.78
LLMF 20.000 h	0.76
LSF¹² 2.000 h	0.99
LSF 4.000 h	0.99
LSF 6.000 h	0.99
LSF 8.000 h	0.99
LSF 12.000 h	0.95
LSF 16.000 h	0.80
LSF 20.000 h	0.50

⁶ Measurement in accordance with IEC 60901

⁷ Electronic Control Gear

⁸ Switching cycle 165 min. on, 15 min. off (according to IEC)

⁹ Average rated lamp life (B50) is the average value of the life time for an entity of lamps operated under standardized conditions until 50% failure. In other words, this is the operation time at which, for a standardized 3-hour switching cycle (165 minutes on / 15 minutes off (according to IEC)), 50% of a sample population of lamps have failed.

¹⁰ Service life time is the mathematical life time (maintenance multiplied with the % of failed lamps e.g. B10) for lamps in an installation after which the installation luminous flux (100 h value) decreased by 30% (decrease in luminous flux and failed lamps) for indoor lighting

¹¹ Lamp Lumen Maintenance Factor (Lamp luminous flux in %): Ratio of the luminous flux of a specific quantity of lamps at a defined number of hours of operation to their luminous flux at 100 h

¹² Lamp Survival Factor (Lamp Survival in %): Ratio of the number of electrically intact lamps to the total number of lamps
Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Energy labelling¹³

Description	Energy efficiency class	Weighted energy consumption E _c [kWh/1000h]
DULUX® D/E 10W/827	A	11
DULUX® D/E 10W/830	A	11
DULUX® D/E 10W/835	A	11
DULUX® D/E 10W/840	A	11
DULUX® D/E 13W/827	A	15
DULUX® D/E 13W/830	A	15
DULUX® D/E 13W/835	A	15
DULUX® D/E 13W/840	A	15
DULUX® D/E 18W/827	A	20
DULUX® D/E 18W/830	A	20
DULUX® D/E 18W/835	A	15
DULUX® D/E 18W/840	A	20
DULUX® D/E 18W/865	A	20
DULUX® D/E 26W/827	A	29
DULUX® D/E 26W/830	A	29
DULUX® D/E 26W/835	A	29
DULUX® D/E 26W/840	A	29
DULUX® D/E 26W/865	A	29

¹³ According to Regulation (EU) No 874/2012 of July 12, 2012
Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.
LP LPD MK

Logistic Data

Description	EAN 10	EAN 40	Packaging Unit
DULUX® D/E 10W/827	4050300012124	4050300245423	10
DULUX® D/E 10W/830	4050300419435	4050300419442	10
DULUX® D/E 10W/835	4050300450933	4050300450940	10
DULUX® D/E 10W/840	4050300017587	4050300251172	10
DULUX® D/E 13W/827	4050300012131	4050300245430	10
DULUX® D/E 13W/830	4050300389059	4050300389066	10
DULUX® D/E 13W/835	4050300450957	4008321577894	10
DULUX® D/E 13W/840	4050300017594	4050300450964	10
DULUX® D/E 18W/827	4050300012148	4050300251189	10
DULUX® D/E 18W/830	4050300327211	4050300962009	10
DULUX® D/E 18W/835	4050300450971	4050300325996	10
DULUX® D/E 18W/840	4050300017617	4050300962054	10
DULUX® D/E 18W/865	4050300564944	4008321577917	10
DULUX® D/E 26W/827	4050300012230	4050300327228	10
DULUX® D/E 26W/830	4050300327235	4050300962047	10
DULUX® D/E 26W/835	4050300450995	4050300450988	10
DULUX® D/E 26W/840	4050300020303	4050300326030	10
DULUX® D/E 26W/865	4008321185877	4050300962030	10

Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Lamp/ECG System Combination

Lamp	ECG	EAN 10 ECG	Luminous flux @25°C [lm]	System power [W]	I _N [A]	Power Factor ECG [λ]	System luminous efficacy [lm/W]	Length [mm]	Width [mm]	Height [mm]	Distance between holes [mm]	T _a [°C]
DULUX® D/E 10 W	QTP-D/E 1x10-13	4008321181572	600	11.5	0.050	0.95	52	93	58	1200	17.5	-20 ... +50
	QTP-D/E 2x10-13	4008321181596	1200	21.0	0.090	0.95	57	123	79	33	129.5	-20 ... +50
	DT-D/E 10-13/220-240 L	4008321181497	600	12.0	0.090	0.6c	50	95	40	64	30.0	-15 ... +50
	DT-D/E 10-13/220-240 C	4008321181510	600	12.0	0.090	0.6c	50	68	Ø = 59			-15 ... +50
	DT-D/E 10-13/220-240 P	4008321181534	600	12.0	0.090	0.6c	50	72	Ø = 59			-15 ... +50
	QT-ECO 1x4-16/220-240 S	4050300638584	600	11.5	0.080	0.6c	52	80	40	22	72-75	-15 ... +50
	QT-ECO 1x4-16/220-240 L	4050300660370	600	11.5	0.080	0.6c	52	150	22	22	140.0	-15 ... +50
	QT-ECO 2x5-11/220-240 S	4050300821504	1200	20.0	0.140	0.6c	60	80	40	22	72-75	-15 ... +50
DULUX® D/E 13 W	QTP-D/E 1x10-13	4008321181572	900	15.0	0.070	0.95	60	93	58	29	96.0	-20 ... +50
	QTP-D/E 2x10-13	4008321181596	1800	29.0	0.130	0.95	62	123	79	33	129.5	-20 ... +50
	DT-D/E 10-13/220-240 L	4008321181497	900	15.5	0.110	0.6c	58	95	40	64	30.0	-15 ... +50
	DT-D/E 10-13/220-240 C	4008321181510	900	15.5	0.110	0.6c	58	68	Ø = 59			-15 ... +50
	DT-D/E 10-13/220-240 P	4008321181534	900	15.5	0.110	0.6c	58	72	Ø = 59			-15 ... +50
	QT-ECO 1x4-16/220-240 S	4050300638584	800	14.0	0.100	0.6c	58	80	40	22	72-75	-15 ... +50
	QT-ECO 1x4-16/220-240 L	4050300660370	800	14.0	0.100	0.6c	58	150	22	22	140.0	-15 ... +50
	DULUX® D/E 18 W	QTi DALI-T/E 1x18-57 DIM	4008321060808	1200	20.0	0.090	0.95	60	123	79	33	129.5
QTi DALI-T/E 2x18-42 DIM		4008321060822	2400	38.0	0.170	0.95	63	123	79	33	129.5	+10...+50
QTi-T/E 1x18-57 DIM		4008321060860	1200	20.0	0.090	0.95	60	123	79	33	129.5	+10...+50
QTi-T/E 2x18-42 DIM		4008321060846	2400	38.0	0.170	0.95	63	123	79	33	129.5	+10...+50
QTP T/E 1x18, 2x18 (1x)		4008321537065	1200	19.0	0.090	0.9c	63	103	67	31	110.0	-20 ... +50
QTP T/E 1x18.. 2x18 (2x)			2400	36.0	0.160	0.98	67					
QTP-T/E 1x18		4008321181701	1200	19.0	0.085	0.98	63	103	67	31	110.0	-20 ... +50
QTP-T/E 2x18		4008321181619	2400	38.0	0.170	0.98	63	123	79	33	129.5	-20 ... +50
DT-T/E 18/230-240 L		4050300406404	1200	17.5	0.100	0.85-0.9c	69	95	40	64	30.0	-20 ... +50
DT-T/E 18/230-240 C		4050300421384	1200	17.5	0.100	0.85-0.9c	69	68	Ø = 59			-20 ... +50
DT-T/E 18/230-240 P		4050300421421	1200	17.5	0.100	0.85-0.9c	69	72	Ø = 59			-20 ... +50
QT-ECO 1x18-21/220-240 S		4050300794907	1150	19.0	0.140	0.6c	61	80	40	22	72-75	-15 ... +50
QT-ECO T/E 2x18/220-240		4050300803982	2300	36.0	0.180	0.95	64	150	41	28	140.0	-15 ... +50

Edition 08.2013. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.
LP LPD MK

Lamp	ECG	EAN 10 ECG	Luminous flux @25°C [lm]	System power [W]	I _N [A]	Power Factor ECG [λ]	System luminous efficacy [lm/W]	Length [mm]	Width [mm]	Height [mm]	Distance between holes [mm]	T _a [°C]
DULUX® D/E 26W	QTi DALI-T/E 1x18-57 DIM	4008321060808	1800	29.0	0.130	0.97	62	123	79	33	129.5	+10...+50
	QTi DALI-T/E 2x18-42 DIM	4008321060822	3600	56.0	0.250	0.98	64	123	79	33	129.5	+10...+50
	QTi-T/E 1x18-57 DIM	4008321060860	1800	29.0	0.130	0.97	62	123	79	33	129.5	+10...+50
	QTi-T/E 2x18-42 DIM	4008321060846	3600	56.0	0.250	0.98	64	123	79	33	129.5	+10...+50
	QTP-M 1x26-42	4008321329134	1750	27.0	0.120	0.95	65	103	67	31	110.0	-20 ... +50
	QTP-M 2x26-32	4008321329158	3500	53.0	0.240	0.97	66	123	79	33	129.5	-20 ... +50
	QTP-M 2x26-42	4008321110022	3600	54.0	0.230	0.97	67	123	79	33	129.5	-20 ... +50
	QTP-T/E 1x26-42, 2x26 (1x)	4008321537089	1750	28.0	0.130	0.95	63	103	67	31	110.0	-20 ... +50
	QTP-T/E 1x26-42, 2x26 (2x)		3500	54.0	0.240	0.98	65					
	QT-ECO 1x26/220-240 S	4008321065971	1600	23.5	0.180	0.6c	68	80	40	22	72-75	-15 ... +50
QT-ECO T/E 2x26/220-240	4050300804002	3500	53.0	0.250	0.95	66	150	41	28	140.0	-15 ... +50	

For more information on ECG refer to <http://www.osram.com/ecg>

For more information on System Guarantee refer to <http://www.osram.com/guarantee>

In case of lamp breakage: www.osram.com/brokenlamp

For more information technical Information see Technical guide. Free download at www.osram.com