

High-performance angular milling cutter 90° with thread

For indexable milling inserts AD.X 0903..

ATORN[®]

Advantage

- Highly positive indexable insert
- Low power consumption
- Precise 90° angular milling



Art. No.	16029 012
Cutting edge diameter	25 mm
Clearance length	33 mm
Length	55 mm
Thread dimension	M12
max. ap	8.5 mm
Number of cutting edges	4 PCS

EAN-Code

4050293389166