



MODEL 2434

Ø28 MAX 100A Resolution 0.1mA AC A DATA HOLD Filter
 AUTO POWER SAVE

- Least affected by external stray magnetic field
- Frequency Selector Switch to eliminate the effect of harmonics
- Minimum resolution 0.1mA

CE

2434	
AC A (50/60Hz)	400mA/4/100A ±2%rdg±4dgt
AC A (WIDE)	400mA/4/100A ±2%rdg±4dgt[50/60Hz] ±3%rdg±5dgt[40 - 400Hz]
Conductor size	φ28mm max.
Frequency response	40 - 400Hz
Effect of external stray magnetic field φ15mm 100A	20mA AC max.
Applicable Standards	IEC 61010-1 CAT III 300V, IEC 61010-2-032
Power source	R03(AAA) (1.5V) × 2 *Continuous measuring time : Approx. 150 hours(Auto power save : Approx. 10 minutes)
Dimension	169(L) × 75(W) × 40(D)mm
Weight	Approx. 220g
Accessories	9097(Carrying case), R03 × 2, Instruction manual

**COSINUS Messtechnik - Ihr Partner für Messlösung
in allen elektrischen und physikalischen Anwendungen**

COSINUS Messtechnik GmbH

Rotwandweg 4

82024 Taufkirchen

Tel.: 089 / 66 55 94 - 0

Fax: 089 / 66 55 94 -30

office@cosinus.de
www.cosinus.de