

Universal chuck

For clamping micro drill bits and milling tools

ATORN[®]

Application

Extremely flexible extension for HYDRO expansion, shrink-fit and collets. For high precision centric clamping of milling, drilling and reaming tools.



Version

- Speed range up to 60,000 rpm
- Concentricity tolerance < 0.005 mm
- Very wide clamping range
- Chuck with spur gear

Art. No.	23720 301
Min./max. clamping width	0.20-3.4 mm
Shaft diameter	16 mm
Outer diameter	19 mm
Length	80 mm
Length 2	50 mm
Max. length	83 mm
Max. tightening torque	2 Nm
Torque transmission	7 Nm
Concentricity tolerance	0.005 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293358377