

Micrometer heads

Large thimble, X-axis

Mitutoyo

Application:

For installation in measuring instruments and presetters, as a setting and control element on machine tools, for fine adjustment of cross tables

Execution:

- With regular gradation
- With simple clamping shank
- Sliding spindle
- Engraved graduation values for each measuring direction have different colours (black or red)



Art. no.	32016 914
Brand	MITUTOYO
Manufacturer Part Number	152-390
Display	Nonius
Min./max. length measuring range	0-25 mm
Scale value	0.005 mm
Measuring surface diameter	6.35 mm
Measuring arrangement	Flat
Clamp in shank diameter	18 mm
Clamping shank length	14 mm
Measuring spindle increments	1 mm
Spindle clamping	No
Design	Metric
Calibration Group	DE
Gross Weight	0.410 kg
Product Group	3MA

EAN

4946368022949