

HID-DynaVision Control for SON

HID-DynaVision Control BSH 250/400 L36 220/240V 50/60Hz HD1-118

HID-DynaVision Controller in combination with electromagnetic systems for SON lamp and continuous dimming

Product data

• General Characteristics

Rated Number of Lamps	1 piece
Rated Ballast-Lamp Power	250/400
Rated Lamptype	SON
Application code	L36
Line Voltage	220/240 V
Line Frequency	50/60 Hz
Design	HD1-118

• Operating Characteristics

Mains voltage safety (AC)	-10%/+10%
Mains voltage performance (AC)	-8%/+6%
Power losses gear	11.0-20.0 W

• Wiring Characteristics

Connector type	Screw
Striplength	7.0 mm
Wcs Ballast contacts	0.70-6.00 mm ²

• Temperature Characteristics

T-storage	-25 (min), 80 (max) C
T-winding maximum (tw)	130 (max) C
Delta-T normal conditions	75 C

• Approval & Application Chars

CE marking	Yes
ENEC certificate	No


• Product Dimensions

Length A1	118.0 mm
Fixing Hole Distance	103.0 mm
Length A2	
Width B1	65.0 mm
Height C1	53.0 mm
Fixing Hole Diameter D1	6.2 mm

• Product Data

Order code	913700239826
Full product code	913700239826
Full product name	BSH 250/400 L36 220/240V 50/60Hz HD1-118
Order product name	BSH 250/400 L36 220/240V 50/60Hz HD1-118
Pieces per pack	1
Packing configuration	6
Packs per outerbox	6
Bar code on pack - EAN1	8711500539847
Bar code on outerbox - EAN3	8711500539854
Logistic code(s) - 12NC	913700239826
Net weight per piece	1.265 kg

Dimensional drawing



Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
B5H 250/400 L36 220/240V 50/60Hz HD1-118	118.0	103.0	65.0	53.0	6.2



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, May 14
data subject to change