

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE

NOTES1:

- UL Standard
- 1.Rated voltage/current : 300V / 15A
- 2.Withstanding voltage : AC1600V/1Min.
- 3.Torque value : M3 , 0.59Lb.in
- 4.Wire range : 28~12AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	18A





- 2.Torque value : M3 , 5.16N·m
- 3.Wire range : 1.0~2.5mm<sup>2</sup>

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 5.08mm, Poles : N=02-24P
- 3.Stripping length : 7~8mm
- 4.Operating temperature: -40°C~+105°C
- 5.Undimensioned tolerances:

Pitch	range		In	Nominal dimension		range	Tolerance
	mm	Over		mm	Over		
6	10	TO	30	60	100	150	0.1/10
TO	TO	TO	TO	TO	TO	TO	≤
6	10	24	30	60	100	150	±2
+0.15 ±0.20 ±0.30 ±0.50 ±0.70 ±1.00 ±1.30							

6.RoHS Compliance



2EDGKB - 5.08 - XXP - 1Y - 1000A (H)  
 (RoHS)  
 (Series No.)(Pitch)(Poles) (Single Pitch) (Color) : 1.(Grey)  
 2.(Blue)  
 3.(Black)  
 4.(Green)  
 5.(Orange)  
 6.(Red)  
 7.(Transparent)  
 8.(Yellow)  
 9.(White)

1000A-(Customer Request)  
 (RoHS)  
 1.(Grey)  
 2.(Blue)  
 3.(Black)  
 4.(Green)  
 5.(Orange)  
 6.(Red)  
 7.(Transparent)  
 8.(Yellow)  
 9.(White)

DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON® NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD:		CHKD:	
DRFT:	WJQ 2017.03.06	TITLE:	CUSTOMER DRAWING
		DRAWING NO.:	
		REV	DO-1
		SHEET	1/1
		SCALE	1:1

