

LOW PROFILE MICROPROCESSOR CRYSTAL Page 1 of 3

AS-16.000-20-EXT


SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	16.000 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±30 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±50 ppm max
OPERATING TEMPERATURE RANGE	-40°C to +85°C
STORAGE TEMPERATURE RANGE	-55°C to +125°C
AGING	±5 ppm per year max
LOAD CAPACITANCE	20 pF
EQUIVALENT SERIES RESISTANCE	40 Ω max
SHUNT CAPACITANCE	5 pF max
DRIVE LEVEL	100 µW typ, 500 µW max
REFLOW CONDITIONS	260°C for 10 sec max



Photo is not actual part

MECHANICAL SPECIFICATION



HEIGHT "H" = 3.5 mm






LOW PROFILE MICROPROCESSOR CRYSTAL Page 2 of 3

AS-16.000-20-EXT

• REFLOW PROFILE



Reflow profile				
Temperature Min Preheat	T _{SMIN}	150°C		
Temperature Max Preheat	T _{SMAX}	200°C		
Time (T _{SMIN} to T _{SMAX})	ts	60-180 sec.		
Temperature	TL	217°C		
Peak Temperature	T _P	260°C		
Ramp-up rate	R _{UP}	3°C/sec max.		
Ramp-down rate	R _{DOWN}	6°C/sec max.		
Time within 5°C of Peak Temperature	t _P	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	tL	60-150 sec.		

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Sn





AS-16.000-20-EXT

MARKING

R160xxAyw

- x Internal Production ID code
- y Year code
- w-Week code

YEAR CODE		
Year	Code	
2011	1	
2012	2	
2013	3	
2014	4	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	

	ALPHA WEEK CODE TABLE				
Week	Code	Week	Code	Week	Code
1	а	19	s	37	K
2	b	20	t	38	L
3	с	21	u	39	М
4	d	22	v	40	Ν
5	e	23	w	41	0
6	f	24	х	42	Р
7	g	25	у	43	Q
8	ĥ	26	z	44	R
9	i	27	А	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	Х
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	I		
18	r	36	J		

APPROVAL

DRAWN BY:	KJackson, June 13, 2019
APPROVED BY:	Jlvens, June 13, 2019
REVISION:	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time withhout notice. Raltron/RAMI Tech does not guarantee that the information is accurate, reliable of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.