

Multi-purpose cabinet with shelves and holders for equipment with handles

Without partition, height 1800 mm

Application:

For secure and clearly-arranged storage of equipment with handles and other parts.

Execution:

- Stable spot-welded steel sheet metal structure with base 50 mm high
- Smooth, overlay-type doors (noise reduction through rubber pads), with integrated reinforcement, hinged on the left and right
- Smooth shelves without raised edges make the lockers easy to clean, ventilation provided by means of holes in the rear wall
- Locks with cylinder security lock, incl. 2 keys

Art. no.	50108 015
Door design	Full-sheet panel
Width	600 mm
Depth	500 mm
Height	1800 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	25 kg
Load-carrying capacity	125 kg
With partition wall	Yes
Central locking	Yes
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Lacquered
Gross Weight	45.000 kg
Product Group	504



EAN

4250618227894