

Contact Tachometer

✓ **For Contact rpm measurements**
Plus Linear surface speed measurements in ft/min or m/min

Features:

- Large 5 digit LCD display is easy to read
- Built-in memory recalls last MAX/MIN value stored
- Autoranging with 0.05% accuracy
- Contact measurements from 0.5 to 19,999rpm plus linear surface speed measures in ft/min or m/min
- Simply contact rotating object with sensor tip and read
- Accessory wheels enable tachometer to measure linear surface speeds
- Complete with cone tip, flat tip and spare wheel for surface speed measurements, four 1.5V AA batteries and case



Accessory wheels enable tachometer to measure linear speed surfaces



Specifications	
Range	0.5 to 19,999rpm 0.2 to 6560ft/min 0.05 to 1999.9m/min
Accuracy	±(0.05%rdg +1d)
Sampling Time	1sec>6rpm
Resolution	0.1rpm (0.5 to 999.9rpm); 1rpm >1000rpm
Dimensions	6.7 x 2.8 x 1.5" (170 x 27 x 37mm)
Weight	9.2oz (260g)

Ordering Information:

- 461891Contact Tachometer
- 461891-NIST461891 with Calibration Traceable to NIST
- 461990Set of Spare Contact Wheels (2 sets of 3)