

### **SOT-23 SURFACE MOUNT LED LAMP**

Part Number: KM-23ID-F High Efficiency Red


### **Features**

- SOT-23 package surface mount LED lamp.
- Low power consumption.
- Long life solid state reliability.
- Package: 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.


### Description


The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

### **Package Dimensions**



- 1 ANODE
- 2 N.C.
- 3 CATHODE





### Notes:

- All dimensions are in millimeters (inches).
   Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. Lead spacing is measured where the lead emerge from the package.
- 4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- 5.The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAA4561 **REV NO: V.16A** DATE: AUG/14/2012 PAGE: 1 OF 5 APPROVED: WYNEC CHECKED: Allen Liu DRAWN: D.M.Su ERP: 1202000019

### **Selection Guide**

Part No.	Dice Lens Type	Lens Type	lv (mo @ 20	Viewing Angle [1]	
		2.	Min.	Тур.	201/2
KW 22ID E	High Efficiency Red (CaAaR/CaR)	Dad Differend	5	12	- 140°
KM-23ID-F	High Efficiency Red (GaAsP/GaP)	Red Diffused	*3	*7	

#### Notes:

- $1. \theta 1/2$  is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity/ luminous Flux: +/-15%.
   \* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

### Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.		Тур.		Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627	*627		nm	IF=20mA		
λD [1]	Dominant Wavelength	High Efficiency Red	625	*617		nm	IF=20mA		
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45			nm	IF=20mA		
С	Capacitance	High Efficiency Red	15			pF	VF=0V;f=1MHz		
VF [2]	Forward Voltage	High Efficiency Red	2		2.5	V	IF=20mA		
lR	Reverse Current	High Efficiency Red			10	uA	V <sub>R</sub> =5V		

- 1.Wavelength: +/-1nm.
  2.Forward Voltage: +/-0.1V.


  \* Wavelength value is traceable to the CIE127-2007 compliant national standards.

### Absolute Maximum Ratings at TA=25°C

arameter High Efficiency Red		Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	160	mA		
Reverse Voltage	5	V		
Operating Temperature	-40°C To +85°C			
Storage Temperature	-40°C To +85°C			


1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAA4561 **REV NO: V.16A** DATE: AUG/14/2012 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1202000019





RELATIVE INTENSITY Vs. WAVELENGTH


#### **High Efficiency Red** KM-23ID-F












SPEC NO: DSAA4561 **REV NO: V.16A** DATE: AUG/14/2012 PAGE: 3 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1202000019

### KM-23ID-F

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


  3.Number of reflow process shall be 2 times or less.


### **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



### **Tape Dimensions** (Units: mm)

### **Reel Dimension**








SPEC NO: DSAA4561 **REV NO: V.16A** DATE: AUG/14/2012 PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1202000019

### PACKING & LABEL SPECIFICATIONS

### KM-23ID-F







Detailed application notes are listed on our website. http://www.kingbright.com/application notes

SPEC NO: DSAA4561 APPROVED: WYNEC REV NO: V.16A CHECKED: Allen Liu DATE: AUG/14/2012 DRAWN: D.M.Su PAGE: 5 OF 5 ERP: 1202000019