

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: ALUMINIUM EPOXY STICK

Product code: 307913 / 89181

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: A two component epoxy repair putty for aluminium.

1.3. Details of the supplier of the safety data sheet

Company name: Jenolite UK Ltd
Chater Lea Buildings
Letchworth
Hertfordshire
SG6 1WT

Tel: 01462 480764

Email: Sales@Jenolite.net

1.4. Emergency telephone number

Emergency tel: 01462 480764
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; -: EUH205

Most important adverse effects: Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. Harmful to aquatic life with long lasting effects. Contains epoxy constituents. May produce an allergic reaction.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

EUH205: Contains epoxy constituents. May produce an allergic reaction.

Hazard pictograms: GHS07: Exclamation mark



SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 2

Signal words: Warning

Precautionary statements: P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.
P264: Wash hands thoroughly after handling.
P273: Avoid release to the environment.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352: IF ON SKIN: Wash with plenty of water.
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P333+P313: If skin irritation or rash occurs: Get medical advice/attention.
P337+P313: If eye irritation persists: Get medical advice/attention.
P501: Dispose of contents/container to comply with Local, National and International regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

TALC

EINECS	CAS	PBT / WEL	CLP Classification	Percent
238-877-9	14807-96-6	Substance with a Community workplace exposure limit.	-	60.000%

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

500-033-5	25068-38-6	-	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Chronic 2: H411	13.240%
-----------	------------	---	--	---------

ALUMINIUM POWDER (PYROPHORIC)

231-072-3	7429-90-5	Substance with a Community workplace exposure limit.	Water-react. 2: H261; Pyr. Sol. 1: H250	2.500%
-----------	-----------	--	---	--------

GLASS, OXIDE, CHEMICALS - REACH registered number(s): 01-2119990048-30

266-046-0	65997-17-3	Substance with a Community workplace exposure limit.	-	2.500%
-----------	------------	--	---	--------

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

202-013-9	90-72-2	-	Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315	2.000%
-----------	---------	---	---	--------

Section 4: First aid measures

[cont...]

SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 3

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not create dust.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

[cont...]

SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 4

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

Do not handle in a confined space. Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

TALC

Workplace exposure limits:

Respirable dust:

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	-	1 mg/m ³	-

ALUMINIUM POWDER (PYROPHORIC)

UK	10 mg/m ³	30 mg/m ³	-	-
----	----------------------	----------------------	---	---

GLASS, OXIDE, CHEMICALS

UK	5mg/m ²	-	-	-
----	--------------------	---	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency. Respiratory protective device with particle filter.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 5

9.1. Information on basic physical and chemical properties

State: Solid

Colour: Grey

Odour: Barely perceptible odour

Solubility in water: Insoluble

Flash point°C: >100

Vapour pressure: <500 Pa 50degC

Relative density: 1.95

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
ORAL	RAT	LD50	11400	mg/kg

Hazardous ingredients:

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

ORL	MUS	LD50	15600	mg/kg
-----	-----	------	-------	-------

[cont...]

SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 6

ORL	RAT	LD50	11400	mg/kg
SKN	RBT	LD50	>20	ml/kg

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

ORL	RAT	LD50	1200	mg/kg
SKN	RAT	LD50	1280	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Insoluble in water. Floats on water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

[cont...]

SAFETY DATA SHEET

ALUMINIUM EPOXY STICK

Page: 7

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 04 09

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH205: Contains epoxy constituents. May produce an allergic reaction.

H250: Catches fire spontaneously if exposed to air.

H261: In contact with water releases flammable gases.

H302: Harmful if swallowed.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.