

## Knurl cutter holder model LA/KFC602

For knurl milling on conventional and automatic lathes



### Application:

For producing knurled milling profiles to DIN 82 RGE 45° and RGE 30° in the steel, stainless steel, non-ferrous metals and cast iron material groups.

### Execution:

- High-strength steel tool holder for two knurl cutters, with carbide bushings

### Advantage:

- Compact and robust holder design for high process stability with small components
- User-friendly adjustment without disassembly
- Carbide bushings minimise maintenance costs



<b>Art. no.</b>	<b>19100 572</b>
<b>Brand</b>	QUICK
<b>Manufacturer Part Number</b>	32000365
<b>For min. workpiece diameter</b>	1.5 mm
<b>For max. workpiece diameter</b>	12 mm
<b>Suitable for knurling wheel diameter</b>	8.9 mm
<b>Shank width</b>	12 mm
<b>Shaft height</b>	12 mm
<b>Tool design</b>	Right
<b>Gross Weight</b>	0.182 kg
<b>Product Group</b>	192