

Revolving high-performance tips

With reinforced bearings



Application:

For use in conjunction with conventional turning, CNC turning, rough machining and smoothing.

Execution:

- 60° moving point.
- For all turning operations (roughing, finishing and fine turning).
- Precision and rough machining of medium-sized components.
- Hardened and precision-ground.

Advantage:

- Long service life.
- Concentricity guaranteed with test report.
- Maintenance-free owing to permanent lubrication.
- Reinforced and hard-wearing precision bearings to absorb radial and axial forces.

Delivery:

1x revolving high-performance tips.



| | |
|-------------------------------------|------------------|
| Art. no. | 22130 020 |
| Brand | BRUCKNER |
| Manufacturer Part Number | 5002 |
| Morse taper size | MK 2 |
| Programming size | 82 mm |
| Programming size for housing | 57 mm |
| Max. workpiece weight | 280 kg |
| Max. rotation speed | 5500 rpm |
| Concentricity tolerance | 0.005 mm |
| Diameter of housing | 45 mm |
| Tip diameter | 20 mm |
| Gross Weight | 0.719 kg |
| Product Group | 2AA |