

Vertical quick-action clamp

With open clamping arm and horizontal base



Application:

For quick clamping of workpieces.

Execution:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

Delivery:

With thrust bolt and protective cap



Art. no.	26212 050
Brand	AMF
Manufacturer Part Number	90050
Size	5
Min./max. distance between stop and centre of drill	45-50 mm
Bore diameter	8.5 mm
Clamping height	55.8 mm
Retaining force	3000 N
Max. tensile force	5000 N
Height	281 mm
Length, clamped	195 mm
Length, open	195 mm
Thumbscrew size	M12 x 80 mm
Gross Weight	1.474 kg
Product Group	260

EAN

4020772090050