

horizontal clamp with variable clamping height

with open clamping arm and vertical base



Application:


Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 20 clamping bolt M6 x 40 mm
- Size 50 clamping bolt M8 x 39 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



Art. no.	26215 620
Size	50
Distance	8.4 mm
Basic length	106.5 mm
Elongated hole spacing	38 mm
Drill hole	6.5 mm
Drill hole 2	6.5 mm
Length 2	35 mm
Length 3	50 mm
Height	59 mm
Overall height of lower handle	94.5 mm
Overall height of upper handle	158 mm
Max. adjustment range	42 mm
Min. adjustment range	27.5 mm
Thickness	13 mm
Distance 2	8.5 mm
Base plate length 2	19 mm
Length	243 mm
Min./max. elongated hole spacing	45-49 mm
Hole distance	49 mm
Base plate width	21 mm
Base plate thickness	4 mm
Base plate length	55 mm
Tension force	3 kN
Height 2	35 mm

EAN-Code

4020772003685